



Actual

**Catalog Number:** TY33M  
**Product ID:** 7TAG009520R0046  
**UPC Number:** 78621082485  
**EAN Number:** 05414363064190  
**Status:** Active

Integrated Mounting Hole Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, Length of 101.61mm (4.0 Inches), Width of 2.31mm (0.09 Inches), Thickness of 0.92mm (0.036 Inches), Tensile Strength Rating of 80 Newtons (18 pounds), #4 Screw for Mounting, Bulk Pack

- Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
- Because there are no notches, Ty-Rap ties provide an infinite number of locking positions while fastening the tie at the precise bundle diameter needed.
- The No-Slip Tail provides easy grip during tensioning. Ty-Rap ties feature a unique friction surface designed to reduce slippage during installation.
- Smooth, notchless body reduces stress concentration points under tension, making the tie stronger and lower profile than notched body ties. Ribbed and Stippled body grips the bundle and prevents slippage. Rounded edges protect insulation, preventing sharp edges from damaging cables.

### North American Specifications (UNSPSC)

UNSPSC	39121703 Cable ties
IGCC	5037 Cable Ties & Wraps
Brand Name	Ty-Rap
Type	Mounting Head
Special Features	Low profile head is designed to prevent snags on uneven surfaces and easier to pull through bulkheads. Non-magnetic stainless steel locking device insures both maximum strength and the right tightness every time.
Standard	UL E49405
Width	0.09 Inches/2.31mm
Length	4.0 Inches/101.61mm
Thickness	0.036 Inches/0.92mm
Bundle Diameter	0.08 Inches/2mm-0.63 Inches/16mm
Material	Nylon/Polyamide 6.6
Color	Natural
Lock Mechanism	Double Locking Head
Tensile Strength	18 Pounds/80 Newtons

### European Specifications (ETIM)

ETIM	EC000046 Cable tie
Band width	2.31mm
Length belt/tape/tie	101.61mm
Tie thickness	0.92mm
Max. bundle diameter	16mm
Min. holding force	80N
Operating temperature	-40-+85°C
Model	Internal toothing
Band closure	Double lock head
Material	Plastic
Material quality	Polyamide PA
Surface protection	Untreated
UV-stable acc. ASTM D6779	N
Halogen free	Y

Colour	Natural colour
Transparent	N
Reflective (fluorescent)	N
Text strip	None
Solvable fastener	N
Type of fastening	Screw hole
VG approval	N
MIL approval	N
UL approval	N

**Packaging**

Inner Quantity	1000
Inner Dimensions (inches)	8.2x4.9x3.6
Outer Quantity	10000
Outer Dimensions (inches)	10.3x10.1x9.2
Weight Uom	0.63 lbs. per 1000

**Documents / Support Tools**

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com