



E-Z-Code*

T&B Catalog Number: WM-123 78621080609

Description: Standard Wire Marker Books - Vinyl Cloth

150 Markers each: 1, 2, 3

Status: Active

Images	
lmage_1_s7	wm045_ez1
Features	
	Pocket pack wire marker books are easy to car- ry and easy to use. The material is an all-purpose vinyl coated cloth tape exclusively designed to re- sist abrasion, oil, water, and dirt.
	Choose the numbers or letters you need. Wide selection of sizes and legends.
	Cover keeps markers clean. Books are 3 x 5 1/2 inches - pocket size.
General	
Style	Vinyl Cloth
Number of Markers and Legends	150 Markers each: 1, 2, 3
Legend	1 - 3
Packaging	
T&B Order Multiple	10
T&B Inner Pack	1
Package in Units	10
T&B Sold in UOM	Each
T&B Weight Per UOM	15.09 lbs. per 100
Application Support	
Overview	Available on Website
Notes	
	10 Pages per book.
	Order Multiple 25 cards.
Certifications	
RoHS Compliance	Yes

Wire Marker Books

E-Z-Code°

Markers that withstand oil, water and humidity!

Vinyl Cloth, Standard Books

- · Choose the numbers or letters you need
- Wide selection of sizes and legends
- Size 3" x 5" (76 mm x 146 mm)
- · Material: vinyl cloth
- · Cover keeps markers clean
- . Books are 3" x 51/2" pocket size
- · 10 pages per book

Pocket pack wire marker books are easy to carry, and easy to use. The material is an all-purpose viryl coated cloth tape exclusively designed to resist abrasion, oil, water, and dirt.

From Thomas & Betts you get the one-piece wire marker and terminal marker. A slight die-cut enables you to easily remove the terminal marker if you need it or leave it in place for a longer marker.



	Thomas Betts
	E-Z-Code®
	Pocket Pack Wire Markers
	WM-0-45 13 markers each 0 thru 45
u	7 86210 80607 5
0	1 7 E Mexico

GAT, NO.	NUMBER OF MARKERS AND LEGENDS
WM-0 thru 9	40 Markers each: 0 thru 9; 10 Markers each: 11, 12, 13, L1, L2, L3, WM-0 thru -9
WM-0-9M	46 Markers each page; full page of 1, full page of 2, etc.
WM-0-45	10 Markers each: 0 thru 45
WM-46-90	10 Markers each: 46 thru 90
WM-A-Z	10 Markers each: A thru Z, +, -, and 0 thru 15
WM-123	150 Markers each: 1, 2, 3
WM-ABC	150 Markers each: A, B, C
WM-A-33	10 Markers each: 1 thru 33, A, B, C, +, -, T1, T2, T3, L1, L2, L3
WM-A-90	6 Markers each: 0 thru 15; 4 Markers each: 1
WM-0 thru WM-9	6 thru 90: 2 Markers each; A thru Z 460 Markers each of any number 0 thru 9
WM-A, -B, -C, -D, -E, -F, -G, -L, -M, -P, -R, -S, -T, or X	460 Markers each of any letter: -A, -B, -C, -D, -E, -F, -G, -L, -N, -P, -R, -S, -T or X
WM-GRD	120 Markers: %," x 2%" or 240 Markers: %," x 1%" with "GRD" legend
WMLC-1	24 Legends, 2 legends each per page, 480 Markers per book for house wiring and circuit breakers: %" x %" (16mm x 10mm)

NUMBER OF MARKERS AND LEGENDS
10 Pages T., T., T.; 140 Markers ea.; total 420
10 Pages L., L., L.; 140 Markers ea.; total 420
3 Pages 1, 2, 3; 42 Markers ea.;
3 Pages A, B, C; 42 Markers ea.;
2 Pages T., T., T.; 28 Markers ea.;
2 Pages L., L., L.; 28 Markers ea.; total 140
10 Pages 1-30; 14 Markers ea.; total 140
A-Z 8% Pages, 14 Markers ea.;
Blank Write Ons 1 Page, 22 Markers ea.;
Plus & Minus X Page, 7 Markers ea.; total 393
Plus & Minus, AC, DC, 1 Page ea., 46 Markers ea.;
Pos. Neg. 6nd. 1 Page ea., 28 Markers ea.;
Spare, Neut. 1 Page ea.,
22 Markers ea.; Blank Write-Ons 1 Page ea.,
22 Markers ea.; total 296
5 Pages ea. 0-45; 5 Markers ea.;
5 Pages ea. 45-90; 5 Markers ea.; total 455

Order multiple 10 books