



Representative

**Catalog Number:** 54134  
**Product ID:** 7TAH007100R0025  
**UPC Number:** 78621054134  
**EAN Number:** 05414363143444  
**Status:** Active

Copper One-Hole Lug, Standard Barrel, Peep Hole, Max 35kV, Wire Size #6 AWG, #10 Bolt Size, Tin Plated, Die Code 24, Die Color Code Blue, 50 Pieces

### North American Specifications (UNSPSC)

UNSPSC	39121405 Cable or wire lug
IGCC	4532 Cable or wire lug
Brand Name	Color-Keyed
Type	Standard Barrel Copper Lug
Standard	UL E9809
Cable Size	#6 AWG
Stud Size	#10
Number Of Holes	1
Material	Copper
Color	Blue

### European Specifications (ETIM)

ETIM	EC001051 Tube cable lug for copper conductors
Connecting angle	Straight
Slender flange model	N
With sight-hole	Y
Material	Copper
Surface protection	Tinned
Number of fixing holes	1

### Packaging

Inner Quantity	50
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	500
Outer Dimensions (inches)	12.8x6.3x4
Weight Uom	1.5 lbs. per 100

### Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)