



Actual



Representative

Catalog Number: 2932NM
Product ID: 7TAD105200R0003
UPC Number: 78621079745
EAN Number: 05414363101819
Status: Active

Liquidtight Strain Relief Connector, Straight, 3/4 Inch NPT Thread, Cable Range 0.500 Inch/12.7mm to 0.750 Inch/19.0mm, IP65 Rating, UV Resistant Polyamide 6.6 Body, Black

- Extended range with superior strain relief.
- Reduced overall size, fits into tighter spaces.
- Gland nut designed to restrict cable bending.
- Provide a means for passing a cord cable into an enclosure through a bulkhead
- Suitable for Ordinary, Wet or Dry locations.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Cord Connectors-Straight
Special Features	Extended Range with Superior Strain Relief
Application	Provide a Means for Passing a Cord Cable Into an Enclosure Through a Bulkhead
Standard	UL E13938, CSA 52391
Size	3/4 Inch
Conductor Range	0.500 Inch/12.7mm to 0.750 Inch/19.0mm
Material	Polyamide/Nylon 6.6
Color	Black
Temperature Rating	-34 to +105 Degrees C
Environmental Conditions	Ordinary, Wet, or Dry Locations

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	15.875mm
Suitable for cable diameter	12.7-19.0mm
Material	Plastic
Material quality	Polyamide (PA)
Degree of protection (IP)	IP65
Colour	Black
Model	Straight
Strain relief	Y
Operating temperature	-34-+105°C

Packaging

Inner Quantity	10
Inner Dimensions (inches)	6x4.5x3
Outer Quantity	100
Outer Dimensions (inches)	12.75x11x8.75
Weight Uom	7.63 lbs. per 100

Documents / Support Tools

Technical Data Sheet US Available on Website

Technical Data Sheet CA
Instruction Sheet 1

Available on Website
ta00927-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com