

54505



Color-Keyed®

Two-way splice connector. Standard barrel for 600 V and recommended up to 35 kV applications. Colour key Blue.

General

T&B Instruction Sheets:	TA00676-TB2
Type:	Compression Connectors for Copper Conductors
Finish:	Electro-Tin Plated
Application:	For 600 V and recommended up to 35 kV
T&B UPC:	78621054505
T&B Status:	M
Material:	High-Conductivity Cast Copper

Dimension Information

Wire Size:	#6 AWG
Barrel Length:	Standard
Die Code No.:	24