



Actual



Actual

Catalog Number: LTC100-TB
Product ID: 7TAD012610R0010
UPC Number: 78621078956
EAN Number: 05414363134879
Status: Active

Industrial Grade, Type B Liquidtight Flexible PVC Conduit, 1 Inch Conduit Size, Approved for Outdoor and Direct Burial in the US, UL Temperature Ratings - 105 Degrees C Dry, 60 Degree C Wet, 70 Degree C Oil, CSA Temperature Rating 18 to 75 Degrees C, Oil Resistant, Voltage Rating 600V, Black with Orange Markings

- Fast installation, even in tight or cramped spaces.
- Smooth inner diameter allows easy wire pulling.
- Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.
- Lightweight and liquidtight.

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	T&B
Type	Liquidtight Flexible Non-Metallic Conduit
Special Features	The Smooth Inner Surface Ensures that Cables and Conductors Can Be Fed Through Very Easily
Application	Machine Tools, Motor Hookups, Food Processing Equipment, Extensions from Wire Ways, and Sensor and Micro Switch Wiring Found In Control Consoles.
Standard	UL E95745, CSA
Trade Size	1 Inch
Outside Diameter	33.4mm
Inside Diameter	26.4mm
Length	30.5 Meters
Voltage Rating	600 Volts
Material	PVC
Color	Black

European Specifications (ETIM)

ETIM	EC001177 Protective plastic hose
Nominal size in inch	1 inch
Material	PVC
Operating temperature	-18-+105°C
Flexibility	Flexible
Colour	Black
Approved according to CSA	Y

Packaging

Outer Quantity	100
Outer Dimensions (inches)	24.5x24.25x8.5
Weight Uom	30.31 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
-------------------------	----------------------

For further technical assistance, please contact us...

8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com