



Actual

Catalog Number: EFC200
Product ID: 7TAD012730R0007
UPC Number: 78621078966
EAN Number: 05414363100355
Status: Active

2 Inch Black Corrugated PVC Flexible Tubing

- Extremely fast installation
- Liquidtight with specified fittings.
- Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.

North American Specifications (UNSPSC)

UNSPSC	39131706 Electrical conduit
IGCC	5535 Electrical conduit
Brand Name	T&B
Type	Type B Liquidtight Tubing & Fittings
Special Features	Maximum Flexibility In Tight Applications.
Application	Protection of Fiber Optic Cable, Installation of Instrumentation and Control Cable, Indoor and Outdoor Lighting, Packaging Equipment, Marine and Shipboard Wiring, and Flexing-Component Wiring Protection on Robots, Graphic Arts Equipments, Etc.
Standard	E 96548
Trade Size	2 Inches
Material	PVC
Color	Black

European Specifications (ETIM)

ETIM	EC001175 Corrugated plastic hose
Nominal size in inch	2 inch
Material	PVC
Operating temperature	-18-+60°C
Oil resistant	Y
Colour	Black
Lengthwise slotted	N
Closable (two-part)	N

Packaging

Outer Quantity	50
Outer Dimensions (inches)	39x12.3x38.5
Weight Uom	52 lbs. per 100

Documents / Support Tools

Technical Data Sheet US [Available on Website](#)

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com