



Representative

Catalog Number: LT475P
Product ID: 7TAD012550R0011
UPC Number: 78621045083
EAN Number: 05414363100669
Status: Active

3/4 Inch 45 Degree Non-Metallic Liquidtight Bullet Connector

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.
- Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Bullet-45 Degree
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	3/4 Inch
Material	Thermoplastic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	3/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	14.78mm
Material screw gland	Other
Material sealing	Other
Colour	Black

Packaging

Inner Quantity	10
Inner Dimensions (inches)	8x5x4
Outer Quantity	50
Outer Dimensions (inches)	27x8.75x5.25
Weight Uom	13.75 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	ta00970-tb2
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00998-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com