



Representative

Catalog Number: LT4125P
Product ID: 7TAD012570R0000
UPC Number: 78621045085
EAN Number: 05414363100614
Status: Active

1-1/4 Inch 45 Degree Non-Metallic Liquidtight Bullet Connector

- Outside surface has friction reducing ridges.
- Inner surface teeth bite into conduit or tubing to enhance clamping and sealing action.
- Fitting ferrule designed to accept variations in conduit sizes and field conduit cuts.
- Smooth ferrule profile reduces friction to ensure a tight conduit-to-fitting seal.
- Suitable for hazardous locations; Class I Div 2; Class II Div 1 & 2; Groups E, F, G; Class III per N.E.C.; Article 501-4, 502-4 and 503-3

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Bullet-45 Degree
Application	T&B Bullet meets performance requirements when terminating Type B liquidtight non-metallic conduit or flexible non-metallic tubing to a box or enclosure with knockout opening or threaded hub.
Standard	UL E23018, CSA
Size	1-1/4 Inch
Material	Thermoplastic

European Specifications (ETIM)

ETIM	EC001178 Screw connection for protective plastic hose
Nominal size in inch	1 1/4 inch
Model	45°-elbow
Revolving thread	N
Construction type	External thread
Type of connection	Thread
Thread connection size	Other
Thread length	19.05mm
Material screw gland	Other
Material sealing	Other
Colour	Black

Packaging

Inner Quantity	2
Inner Dimensions (inches)	6.2x5.1x4.3
Outer Quantity	10
Outer Dimensions (inches)	26.2x6.7x5.2
Weight Uom	30 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	ta00970-tb2
Technical Data Sheet CA	Available on Website
Instruction Sheet 1	ta00998-tb2

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com