



Actual



Representative

Catalog Number: 2520
Product ID: 7TBD105230R0000
UPC Number: 78621002520
EAN Number: 05414363101581
Status: Active

Liquidtight Strain Relief Cord Connector, 1/2 Inch, Straight, Cord Range 0.125 to 0.250 Inch, Die Cast Zinc

- Meets Coast Guard CG293

Header

3D Model Available on Website

North American Specifications (UNSPSC)

| | |
|--------------------|--|
| UNSPSC | 39121431 Cable gland connector |
| IGCC | 4601 Cable gland connector |
| Brand Name | T&B |
| Type | Strain Relief Cord Connectors-Straight |
| Special Features | Meets Coast Guard CG293 |
| Application | Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B). |
| Standard | UL E13938, CSA |
| Size | 1/2 Inch |
| Conductor Range | 0.125 to 0.250 Inch |
| Material | Zinc Die Cast |
| Color | Metallic |
| Temperature Rating | 105 Degrees C |

European Specifications (ETIM)

| | |
|--|----------------------------|
| ETIM | EC000441 Cable screw gland |
| Thread type | NPT |
| Nominal thread size inch/gas pipe thread | 1/2 inch |
| Thread length | 15.875mm |
| Suitable for cable diameter | 3.175-6.35mm |
| Material | Metal |
| Material quality | Other |
| Colour | Natural colour |
| Model | Straight |
| Strain relief | Y |
| Operating temperature | 0-+105°C |

Packaging

| | |
|---------------------------|-------------------|
| Inner Quantity | 25 |
| Inner Dimensions (inches) | 5x4.5x3 |
| Outer Quantity | 100 |
| Outer Dimensions (inches) | 10.75x10x4 |
| Weight Uom | 12.5 lbs. per 100 |

Documents / Support Tools

| | |
|-------------------------|----------------------|
| Technical Data Sheet US | Available on Website |
| Technical Data Sheet CA | Available on Website |

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289

