

T&B° Fittings



T&B Catalog Number:	EFC03
UPC Number:	786210
Description:	3/8" Bla
-	F

EFC038 78621078960 3/8" Black Corrugated PVC flexible tubing. For use with Bullet® Liquidtight Fittings.

Status:

Feeturee

Active



Features			
	Maximum flexibility in tight applications.		
	Extremely fast installation		
	Liquidtight with specified fittings.		
	Good tensile strength provides excellent pullout		
	protection and smooth inner diameter allows easy		
	wire pulling.		
General			
Material	PVC		
Color	Black		
Conduit Size (inches)	3/8		
Recommended industrial applications	Protection of fiber optic cable, installation of instru-		
	mentation and control cable, indoor and outdoor		
	lighting, packaging equipment, marine and ship-		
	board wiring, and flexing-component wiring protec-		
	tion on robots, graphic arts equipments, etc.		
Dimension Information			
I.D Minimum (inches)	.484		
I.D Maximum (inches)	.504		
O.D Minimum (inches)	.690		
O.D Maximum (inches)	.710		
Packaging			
T&B Order Multiple	100		
Package in Units	100		
T&B Sold in UOM	Feet		
T&B Weight Per UOM	10.25 lbs. per 100		
Application Support			
Guide to Nonmetallic Conduit Applicatio	nsAvailable on Website		
XTRAFLEX System Specifications	Available on Website		
Notes			
*Note	OEM Grade U.L. Recognized		
**Note	Broad operating temperature range - 18° C to +60° C (-2° F to +140° F)		
***Note	Flammability rating VW-1 (vertical wire) UL 224.		
Certifications			
RoHS Compliance	Yes		
Certifications			



File Nbr: E 96548

T&B Fittings

XTRA FLEX[®] System –

Conduit, Tubing, Fittings for Non-Metallic Liquidtight Conduit Material — PVC

Maximum flexibility for tight applications! Corrugated Flexible Non-Metallic Tubing



- OEM grade UL Recognized
- PVC material
- · Black color standard
- · Extremely fast installation
- · Liquidtight with specified fittings
- · Good tensile strength provides excellent pullout protection
- · Smooth inner diameter allows easy wire pulling
- Broad operating temperature range: 18° C to +60° C (-2° F to +140° F).
- Flammability Rating WW-1 (Vertical Wire) UL224

	CONDUIT	I.D. (IN.)		0.D. (IN.)	
CAT. NO.	SIZE	MIN.	MAX.	MIN.	MAX.
EFC025	54°	.390	.405	.560	.575
EFC038	35	.484	.504	.690	.710
EFC050	5	.622	.642	.820	.840
EFC075	35	.820	.840	1.030	1.050
EFC100	1"	1.041	1.066	1.290	1.315
EFC125	1%*	1.380	1.410	1,630	1.660
EFC150	1%"	1.575	1.600	1.865	1.900
EFC200	2"	2.020	2.045	2.340	2.375
* Not CSA Co Underwriters UL File No. 9	Recognized	See tech	No. 067241 nical dala next page. Bullet® Liquidtight I		

AVAILABLE COLORS CAT. NO. LTC -COLOR OF CONDUIT W/O SUFFIX -1 Orange -2 Blue

Recommended industrial applications

- · Protection of fiber optic cable
- · Installation of instrumentation and control cable
- Indoor/outdoor lighting
- Packaging equipment
- · Marine and shipboard wiring
- Flexing component wiring protection on robots, graphic arts equipment, etc.

