



Actual



Representative

Catalog Number: 2535
Product ID: 7TBD105230R0004
UPC Number: 78621002535
EAN Number: 05414363139386
Status: Active

Liquidtight Strain Relief Cord Connector, 3/4 Inch, Straight, Cord Range 0.625 to 0.750 Inch, Die Cast Zinc

- Meets Coast Guard CG293

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	39121431 Cable gland connector
IGCC	4601 Cable gland connector
Brand Name	T&B
Type	Strain Relief Cord Connectors-Straight
Special Features	Meets Coast Guard CG293
Application	Suitable for Use In Hazardous Locations Where General Purpose Equipment is Specifically Permitted by NEC 501-4(B).
Standard	UL E13938, CSA
Size	3/4 Inch
Conductor Range	0.625 to 0.750 Inch
Material	Zinc Die Cast
Color	Metallic
Temperature Rating	105 Degrees C

European Specifications (ETIM)

ETIM	EC000441 Cable screw gland
Thread type	NPT
Nominal thread size inch/gas pipe thread	3/4 inch
Thread length	14.287mm
Suitable for cable diameter	15.875-19.05mm
Material	Metal
Material quality	Other
Colour	Natural colour
Model	Straight
Strain relief	Y
Operating temperature	0-+105°C

Packaging

Inner Quantity	25
Inner Dimensions (inches)	4x4x3
Outer Quantity	100
Outer Dimensions (inches)	12.75x10.75x4.75
Weight Uom	18.44 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289

