



Project: EP Minerals
Location: Reno, NV

Wedco Inc
 450 Toano Street
 Reno, NV, 89512

SNA Terminal Blocks
T&B Catalog Number:

UPC Number: 016511316
 66201996020
Status: Active
Description:

Green and yellow ground block with screw clamp connection, 6 mm spacing on a DIN 3 rail without screw

Features

- Top entry wire connection
- Touch-safe IP20 protection

Application

For use with applications ranging from standard distribution and control panels, to specialized applications in key industries such as traction, energy, maritime, explosive atmospheres, material handling, etc.

General

Style	Ground Block
Color	Green and Yellow
Mounting	DIN 3
Series	M 4/6.P
Connection Technology	Screw Clamp
UL Wire Range (AWG)	22-10
Rated IEC Wire Range (Solid) (mm ²)	0.2 - 4
Rated IEC Wire Range (Stranded) (mm ²)	0.22 - 4

Dimension Information

L x W x H (mm)	43.5 x 6 x 48
Spacing (mm)	6
L x W x H (in)	1.72 x .238 x 1.89
Spacing (inches)	.238

Specifications

Rated UL Wire Size (AWG)	10
--------------------------	----

Packaging

T&B Order Multiple	50
T&B Inner Pack	50
Package in Units	1000
T&B Sold in UOM	Each
T&B Weight Per UOM	4.5 lbs. per 100

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com