



Battery Holders

Manufactured from quality moulding and metal components to ensure a secure and reliable connection, Bulgin's battery holder range caters for battery sizes 1/2AA, AAA(R03), AA(R6), C(R14), D(R20) and PP3(6R61), accommodating 1, 2, 3 or 4 cells.

There's a choice of fixing styles including screw and flange panel fixing, PCB and base mounting versions.

Panel mounting versions are now available in two styles: standard fixing and panel sealed to IP67, extending the applications into harsher external environments where dust or water would inhibit equipment operation.

The open frame styles are designed to be either PCB or base mounted and most have an interlocking facility to join adjacent holders together.

Principle applications include portable equipment and memory back-up.


Туре	Cell Size	Page				
Panel Mounting (sealed to IP67)						
BXS011/1-BXS013/1	AA	9				
BXS001/1-BXS003/1	С	9				
BXS016-BXS018	D	9				
Panel Mounting						
BX0011/1-BX0013/1	AA	10				
BX0027	AA	10				
BX0001/1-BX0003/1	С	10				
BX0016-BX0018	D	11				
BX0023	PP3	11				
BX0026	PP3	11				
PC/Base Mounting						
BX0031	1/2AA	12				
BX0034	AAA	12				
BX0035	AA	12				
BX0036	С	13				
BX0037	D	13				
BX0033	PP3	13				

www.bulgin.co.uk



Battery Holder Selector Maximum Battery Size to BSEN 60086-1 and -2

Battery size	Battery Dimensions	No. of Cells	Mounting	Part No.
1/2AA	Ø14.9 x 25.1	1	PCB/Base	BX0031
AAA (RO3)	Ø10.5 x 44.5	1	PCB/Base	BX0034
AA (R6)	Ø14.5 x 50.5	1 1 2 3 4 1 2 3	PCB/Base Panel Panel Panel Panel Panel Sealed Panel Sealed Panel Sealed	BX0035 BX0011/1 BX0012/1 BX0013/1 BX0027 BXS011/1 BXS012/1 BXS013/1
C (R14)	Ø26.2 x 50	1 1 2 3 1 2 3	PCB/Base Panel Panel Panel Panel Sealed Panel Sealed Panel Sealed	BX0036 BX0001/1 BX0002/1 BX0003/1 BXS001/1 BXS002/1 BXS003/1
D (R20)	Ø34.2 x 61.5	1 1 2 3 1 2 3	PCB/Base Panel Panel Panel Panel Sealed Panel Sealed Panel Sealed	BX0037 BX0016 BX0017 BX0018 BXS016 BXS017 BXS018
PP3 (6R61)	W26.5 x D17.5 x H48.5	1 1 2	PCB/Base Panel Panel	BX0033 BX0023 BX0026




www.bulgin.co.uk



Front panel sealed to IP67


BXS011/1

- 1.2 or 3 Cells
- Flanged Panel Mount
- Bayonet with finger/coin slot release
- Supplied with gasket and sealing grommets for screws






- 1, 2 or 3 Cells
- **Panel Mount**
- Screw Cap/Hand release
- Supplied with gasket



D SIZE BATTERY HOLDER



- 1, 2 or 3 Cells
- Flanged Panel Mount
- Bayonet/finger release
- Supplied with flange gasket and sealing grommets for screws



Specification	BXS011/1, BXS012/1, BXS013/1	BXS001/1, BXS002/1, BXS003/1	BXS016, BXS017, BXS018
Battery/Cell Type:	AA (R6)	C (R14)	D (R20)
No. Cells:	BXS011/1 - 1 cell BXS012/1 - 2 cells BXS013/1 - 3 cells	BXS001/1 - 1 cell BXS002/1 - 2 cells BXS003/1 - 3 cells	BXS016 -1 cell BXS017 - 2 cells BXS018 - 3 cells
Terminations:	2.8 series tabs/solder tags	2.8 series tabs/solder tags	4.8 series tabs/solder tags
Operating Temperature:	-30°C to +70°C	-30°C to +70°C	-30°C to +70°C
Mouldings:	Nylon Glass filled Polyester Polycarbonate	Nylon Glass filled Polyester	Nylon Glass filled Polyester
Flammability Rating:	UL94V-0	UL94V-0	UL94V-0
Contacts:	Brass, Tin Plated - rear contact Nickel Silver, clean - front contact and cap contact plate	Brass, Tin Plated - front and rear contacts Nickel Silver, clean - cap contact plate	Brass, Nickel Plated - front and rear contacts and cap contact plate
Features:	Bayonet cap with finger grip and coin slot Rear support bracket	Screw on cap with finger grip Recommended torque for panel ring 1.13-1.7Nm (10-15lbf.in)	Bayonet cap with finger grip Rear support bracket
Sealing (front of panel):	Protection classification IP67, BS60529:1992	Protection classification IP67, BS60529:1992	Protection classification IP67, BS60529:1992
Notes:	Recommend 2 & 3 cell versions are supported by rear bracket		Recommend 2 & 3 cell versions are supported by rear bracket

www.bulgin.co.uk