



CONTACT • REQUEST A QUOTE

PRODUCTS

RESOURCES

COMPANY

PART NUMBER SEARCH

[« Two Point Pull Handles](#)

## Two Point Pull Handles

### Series #RG

Two-Point or Pull Handle and pocket handle varieties available in phenolic, thermoplastic and thermoplastic overmold materials.

Female insert, tapped thread, pocket and plain molded hole options are available.

New! Soft touch handle is available in 6 standard colors: black, white, red, orange, gray, and yellow.

Click on the part number for additional information and search by diameter, mounting, material, etc.

Colors available upon request.

Please note: Not all variations available are listed below. Please [contact Customer Service](#) to inquire about all available options.



[REQUEST CAD DRAWING](#)   [REQUEST A QUOTE](#)

Item #	Diameter A	Height B	Centers D	Material Type	Mounting Diameter	Mounting Type	Thread Length/Depth
RG-1N.100.09	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1N.100.84	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1N.120.09	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1N.120.84	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1N.140.09	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1N.140.84	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1N.160.09	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1N.160.84	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1N.180.09	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1N.180.84	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1P.100.09	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1P.100.84	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1P.120.09	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1P.120.84	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1P.140.09	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1P.140.84	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1P.160.09	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1P.160.84	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1P.180.09	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1P.180.84	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1S.100.09	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1S.100.84	122	33	100	Thermoplastic	M5	Thru-Hole	0.875
RG-1S.120.09	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1S.120.84	146	39	120	Thermoplastic	M6	Thru-Hole	0.98
RG-1S.140.09	170	45	140	Thermoplastic	M8	Thru-Hole	1.18

RG-1S.140.84	170	45	140	Thermoplastic	M8	Thru-Hole	1.18
RG-1S.160.09	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1S.160.84	194	52	160	Thermoplastic	M8	Thru-Hole	1.375
RG-1S.180.09	218	58	180	Thermoplastic	M10	Thru-Hole	1.57
RG-1S.180.84	218	58	180	Thermoplastic	M10	Thru-Hole	1.57

PRODUCTS

- Knobs
- Handles
- Leveling Feet
- Latches
- Hinges
- Indexing Plungers
- Electronic Enclosures
- Two-Shot / Soft Touch
- Frac Balls
- Custom Molding

RESOURCES

- Engineering Specifications
- Distributor Listing
- Sales Representative Listing

COMPANY

- About Us
- Capabilities
- Certifications
- Contact Us
- Blog
- Careers

QUESTIONS ?

[select your industry]
▼

questions / comments

Copyright © 2016 Davies Molding, LLC. All Rights Reserved.  
 350 Kehoe Blvd. | Carol Stream, IL 60188-1818 | Phone: (800) 554-9208 | Fax: (630) 510-9944