

10 outlet, 10ft cord, 3345 joule rating, 3-line coaxial and 1-line tel/modem/ethernet protection - Home/Business Theater Surge Suppressor

MODEL NUMBER: HT1010SAT3



Description

Tripp Lite's HT1010SAT3 Home/Business Theater Surge Suppressor provides advanced protection--3345 joules--stopping damaging surges and filtering disruptive line noise so components perform at their peak! You can see and hear the difference: sharper, crisper video; deeper, fuller audio and longer component life spans. Perfect for small-to-medium home/business theater installations: high-definition TVs, satellite and A/V receivers, DVD/CD players and more. 10 outlets (with transformer spacing and sliding safety covers), 3-line coaxial protection and 1-line tel/modem/Ethernet (100BaseT, high-speed) protection safeguard an entire home/business theater system. \$250,000 Ultimate Lifetime Insurance coverage (USA and Canada only). Includes two diagnostic LEDs, color-coordinated holographic outlet/plug labels, 10-ft. cord with a right-angle plug, 6-ft. gold DSS cable, 6-ft. coaxial cable, 6-ft. phone cord and 6-ft. network cable.

Features

- 3345 joules surge suppression rating with EMI/RFI line noise filtering help components perform at their peak (sharper, crisper video; deeper, fuller audio and longer component life spans)
- \$250,000 Ultimate Lifetime Insurance (USA and Canada only) covers connected components against surge damage...for life!
- 10 surge-protected NEMA 5-15R AC outlets safeguard an entire home/business theater system
- Widely spaced outlets accommodate up to 5 transformers
- Sliding safety covers protect against accidental contact
- Color-coordinated, holographic outlet/plug labels match outlets with component power cords
- 3 sets of surge-protected Type F gold coaxial connectors (with included 6-ft. gold DSS cable and 6 ft. coaxial cable) safeguard components on cable, satellite and antenna line

Highlights

- 10 outlets / 10-ft. cord
- 3345 joule rating
- 3-line coaxial (gold) surge protection
- 1-line tel/modem/network (100BaseT, high-speed) surge protection
- \$250,000 Ultimate Lifetime Insurance (USA and Canada only)

Package Includes

- HT1010SAT3 Home/Business Theater Surge Suppressor
- 6-ft. gold DSS cable, 6-ft. coaxial cable, 6-ft. phone cord and 6-ft. network cable
- Instruction manual with warranty information



- 1-line tel/modem/Ethernet (100BaseT, high-speed) surge protection (with included 6 ft. phone cord and 6-ft. network cable) safeguards personal video recorders (PVRs) on a single dial-up or Ethernet line. Built-in splitter (1 jack in and 2 jacks out) allows simultaneous connection of two devices sharing a single line
- 10-ft. cord with right-angle NEMA 5-15P plug provides convenient location anywhere within a home/business theater system
- 2 diagnostic LEDs alert user to protection and grounding status
- Keyhole slots provide convenient wall or cabinet mounting
- Master switch provides one-touch power control over all components. Circuit breaker protects against dangerous system overload
- High-impact plastic housing (black) stands up to the most demanding environments
- UL and cUL listed
- Lifetime product warranty

Specifications

OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output (Watts)	1800
Circuit Breaker (amps)	15
Transformer Accommodation	Accommodates 5 transformers
INPUT	
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right-angle input plug
Input Cord Length (ft.)	10
Input Cord Length (m)	3
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Right-Angle Plug	1
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2-position on/off power switch
Diagnostic LED Details	Built-in LEDs confirm protection and grounding status



SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	3345
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330V - UL verified
EMI / RFI Filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	1
Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	1
Cable (Coax) Protection Details	3 line
Network (Ethernet) Protection	1
PHYSICAL	
Shipping Dimensions (hwd / in.)	2.25 x 15 x 9.25
Shipping Dimensions (hwd / cm)	5.7 x 38.1 x 23.5
Shipping Weight (lbs.)	3.53
Shipping Weight (kg)	1.6
Unit Dimensions (hwd / in.)	1.75 x 11.75 x 4.75
Unit Dimensions (hwd / cm)	4.5 x 29.8 x 12.1
Unit Weight (lbs.)	2.42
Unit Weight (kg)	1.1
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting slots allow desk or wall mounting
Color (AC Line Cord)	Black
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$250,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>