

For Patient-Care Vicinity – UL 60601-1 Medical-Grade PS; 4 15A Hospital-Grade Outlets, Safety Covers, 15 ft. Cord

MODEL NUMBER: PS-415-HGULTRA



Description

The PS-415-HGULTRA Medical-Grade Power Strip is the first power strip with full 60601-1 compliance, making it ideal for use in all patient care vicinities. This 120V, 50/60 Hz power strip features a NEMA 5-15P-HG hospital-grade plug and four NEMA 5-15R-HG hospital-grade outlets that include integrated locking safety covers.

A patented protection circuit guards against shock hazards by preventing power from reaching the unit's outlets in the presence of a fault. The protection circuit automatically resets itself and restores power once the fault threat is gone.

Mounting tabs and flanges let you install the PS-415-HGULTRA on a wide variety of surfaces. The all-metal housing ensures safety and is guaranteed to last a long time in demanding environments.

With a switchless design that prevents accidental shutoff and a 15 ft. power cord that can reach a distant power source, the PS-415-HGULTRA is the perfect replacement for all non-compliant power strips. Patent # 7,375,939

Features

Power Distribution Anywhere in Any Medical Facility

- Ideal for use in operating rooms, patient-care vicinities, therapy rooms, imaging environments and administrative areas
- Patented protection circuit guards against shock hazards
- Circuit breaker resets itself once fault threat is gone
- 120V, 50/60 Hz power strip complies with UL 60601-1 and UL 60950-1 specifications

Highlights

- Approved for use in all patient-care vicinities
- Complies with UL 60601-1 and UL 60950-1 specifications
- Patented protection circuit guards against shock hazards
- 4 NEMA 5-15R-HG hospital-grade outlets with locking safety covers
- Includes 15 ft. cord with NEMA 5-15P-HG hospital-grade plug
- Normal 0 false false false EN-US X-NONE X-NONE
MicrosoftInternetExplorer4
- Patent # 7,375,939

Package Includes

- PS-415-HGULTRA UL 60601-1 Medical-Grade Power Strip
- Owner's manual with maintenance requirements



- Patent # 7,375,939

Versatile Medical-Grade Solution

- 4 NEMA 5-15R-HG hospital-grade outlets provide consistent power
- 15-ft. power cord provides ample reach to the power source
- Rugged, all-metal housing for long life in demanding environments

Premium Safety Features

- Integrated locking outlet safety covers block access to unused outlets
- Built-in 15A circuit breaker protects against dangerous overloads
- Switchless design prevents accidental shut-off

Ready to Use Right Out of the Box

- Built-in mounting tabs and flanges make the PS-415-HGULTRA easy to install on a variety of surfaces

Specifications

MODEL TEXT	
Key Benefit	Full 60601-1 compliance, integrated locking safety covers and a 15 ft. cord make this medical-grade power strip ideal for all areas inside and outside of patient care vicinities.
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(4) 5-15R-HG
Circuit Breaker (amps)	15
Overload Protection	15A resettable circuit breaker
Outlet Safety Covers	Yes
Outlet Orientation	Single row of 4
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	15A 120V
Input Connection Type	NEMA 5-15P-HG
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Voltage Compatibility (VAC)	120



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

USER INTERFACE, ALERTS & CONTROLS	
Switches	No power switch
PHYSICAL	
Unit Dimensions (hwd / in.)	1.5 x 13.75 x 2.5
Unit Dimensions (hwd / cm)	3.8 x 34.9 x 6.4
Unit Weight (lbs.)	3.2
Unit Weight (kg)	1.45
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Yes
Receptacle Color	White
Color (AC Line Cord)	White
Outlets Measurement (Center to Center)	92mm
Keyhole Slot Mounting Measurement (Center to Center)	Distance between keyhole tabs = 261.92mm; Distance between end tabs = 334.01mm
CERTIFICATIONS	
Approvals	TUV tested to UL 60601-1 and UL 60950-1 (USA); TUV tested to CAN/CSA-C22.2 No. 601.1-M90 and 60950-1-03 (Canada)
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>