

## Protect It! 6-Outlet Industrial Safety Surge Protector, 15-ft. Cord, 2700 Joules, Cord Wrap, Hang Holes

MODEL NUMBER: TLM615SA



### Description

This Tripp Lite surge suppressor is designed to provide safe, reliable surge protection. A high 2700 joule rating can protect connected equipment against even the strongest surges. 6 outlets protect connected equipment against damaging surges, spikes and line noise. Convenient transformer outlets accommodate multiple transformers without blocking other outlets. A 15 ft. grounded cord with integrated cord clip reaches distant outlets. A lighted on/off switch with integrated circuit breaker provides power control over connected equipment. Breaker protects against dangerous system overload. Protected LED confirms that connected equipment is being protected. 4 safety covers shield unused outlets from debris and accidental contact. Built-in cord wrap with hang holes provides convenient cord management. Integrated keyhole slots on bottom panel provide convenient wall/desk mounting. Tripp Lite will repair or replace any connected equipment damaged by surges, including direct lightning strikes, up to \$75,000 and for life! As an added safety feature, the surge suppressor's bright yellow color alerts you and others that power cords and tools are in use.

### Features

- 6 OUTLETS protect connected equipment against damaging surges, spikes and line noise
- 15 FT. GROUNDED CORD with INTEGRATED CORD CLIP reaches distant outlets.
- LIGHTED ON/OFF SWITCH with INTEGRATED CIRCUIT BREAKER provides power control over connected equipment. Breaker protects against dangerous system overload.
- PROTECTED LED - If this green LED ever goes out, Tripp Lite will replace your surge suppressor under warranty at no charge!
- CONVENIENT TRANSFORMER OUTLETS accommodate multiple transformers without blocking other outlets.

### Highlights

- 6 outlets (including transformer outlets and 4 safety covers)
- 15 ft. cord
- 2700 joule rating
- Cord wrap with hang holes
- Rugged metal case
- \$75,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

### Package Includes

- TLM615SA Safety Surge Suppressor
- 4 safety covers
- Owner's manual



- 4 SAFETY COVERS shield unused outlets from debris and accidental contact.
- RUGGED METAL CASE stands up to harsh indoor use
- CORD WRAP with HANG HOLES provides convenient cord management.
- INTEGRATED KEYHOLE SLOTS on bottom panel provide convenient wall/desk mounting.
- 2700 joules of surge protection
- OSHA color guidelines, outlined in Document 1910.145, alert users to hazardous situations, which may cause minor or moderate injury. This Tripp Lite product complies with those guidelines.
- \$75,000 [Ultimate Lifetime Insurance](#) (U.S., Canada, and Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

## Specifications

OUTPUT	
Frequency Compatibility	60 Hz
Output Receptacles	(6) 5-15R
Circuit Breaker (amps)	15
Overload Protection	Combo power switch and circuit breaker
Transformer Accommodation	Yes (2)
Outlet Safety Covers	Yes (4)
Outlet Orientation	6 in a single row
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Integrated cord clip
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	90000
Right-Angle Plug	0
USER INTERFACE, ALERTS & CONTROLS	



Switches	Combination AC circuit breaker and 2 position lighted on/off power switch
Diagnostic LED Details	1 green "protected" LED confirms surge suppression is present
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	2700
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G/H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400,400,500
EMI / RFI Filtering	Up to 20 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	0
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	7.25 x 2.25 x 16.25
Shipping Dimensions (hwd / cm)	18.42 x 5.72 x 41.28
Shipping Weight (lbs.)	3.54
Shipping Weight (kg)	1.61
Unit Dimensions (hwd / in.)	15.97 x 3.07 x 1.61
Unit Dimensions (hwd / cm)	40.56 x 7.80 x 4.09
Unit Weight (lbs.)	3.24
Unit Weight (kg)	1.47
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Yes
Receptacle Color	black
Color (AC Line Cord)	yellow
Outlets Measurement (Center to Center)	Distance between standard outlets = 30.40mm; Distance between standard and transformer outlets = 45mm
Keyhole Slot Mounting Measurement (Center to Center)	209.55mm
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd EDITION



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Approvals	cULus, RoHS
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$75,000 <u>Ultimate Lifetime Insurance</u>

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>