

NetDirector 8-Port 1U Rack-Mount Console KVM Switch with 17-in. LCD

MODEL NUMBER: **B020-008-17**



Description

Tripp Lite's B020-008-17 KVM Switch gives you a rack-mountable keyboard, LCD and touchpad in a single console that occupies only 1U of rack space. Easy to install and use, it's the optimal solution for controlling up to 8 computers/servers. Increase the number of connected computers to up to 256 by daisy-chaining up to 31 [B022-U08](#) KVM switches

The B020-008-17 has a built-in 17" LCD screen that supports video resolutions up to 1280 x 1024. You can switch easily between the 8 ports using on-console push buttons, an on-screen display (OSD) or keyboard hot key commands. Multi-level password security can be set up for an administrator and up to 4 local users to ensure only those with authorization can access the connected computers.

This switch controls PS/2 or USB computers/servers using a P774-Series (PS/2) or P776-Series (USB) KVM Cable Kit (one of each is included). An extra HD15 port allows an additional VGA monitor to be connected. Two PS/2 ports also are included on the rear of the unit to allow for connection of a Tripp Lite [B051-000](#) IP Remote Access Unit or an external console. When not in use, the B020-008-17 stores neatly in a rack drawer and pulls out when needed. This KVM console is compatible with all major operating systems (special keys on Mac and Sun keyboards are not supported). Heavy-duty steel housing stands up to frequent use.

Features

Saves Valuable Space and Money

- Combines an 8-port KVM switch, 17" LCD screen, full keyboard and touchpad in a 1U rack-mountable drawer
- Mounts into 19"-wide rack, 24"-37" deep

Highlights

- Occupies just 1U of space in a rack-mountable drawer
- 17" LCD screen supports video resolutions up to 1280 x 1024
- Simplifies IT tasks with easy switching between all 8 ports
- Provides 2-level password security (administrator and user)
- Compatible with all operating systems

System Requirements

- PS/2 or USB computer
- (1) P774-Series (PS/2) or P776-Series (USB) KVM Cable Kit is required for each connected computer/server
- Compatible with all major operating systems (special keys on Mac and Sun keyboards are supported)
- Power consumption: 120V, 60Hz, 22.8W; 230V, 50Hz, 24W

Package Includes

- B020-008-17 8-Port Console KVM Switch with 17" LCD
- P774-Series 6 ft. PS/2 KVM Cable Kit
- P776-Series 6 ft. USB KVM Cable Kit
- C13 to 5-15P power cord
- RJ11 to [DB9](#) firmware upgrade cable
- Owner's Manual CD



- Gives you control of up to 8 computers/servers from a single, easily accessible console – ideal when rack space is at a premium
- Flip-up/fold-down screen keeps the console from blocking access to rack equipment when not in use
- Eliminates need to buy costly separate monitors, keyboards and mice for each computer/server

Simplifies IT Tasks

- Switch quickly and easily between the 8 ports via on-console buttons, on-screen display or keyboard hot key commands
- Hot pluggable; add or remove computers without having to power down the switch
- Auto-scan mode automatically sequences through all active ports that are accessible to the user

Large 17" LCD

- Wide display makes multitasking easier
- Supports video resolutions up to 1280 x 1024
- DDC emulation allows the video settings of each computer to be automatically adjusted for optimal output to the LCD

Multi-Level Password Security

- Enhances security by limiting access to an administrator and up to 4 local users
- Two-level log-out allows for manual log-out or automatic log-out after a user-defined period of time has passed

Expandability and Long-Lasting Reliability

- Increase the number of connected computers to up to 256 by daisy-chaining up to 31 [B022-U08](#) KVM switches
- Includes additional HD15 VGA monitor port and PS/2 keyboard/mouse ports for connecting an external console or a Tripp Lite [B051-000](#) IP Remote Access Unit
- Compatible with all major operating systems for easy integration into your existing structure (special keys on Mac and Sun keyboards are not supported)
- Firmware is easily upgradable with included cable and utility
- Heavy-duty steel housing stands up to frequent use

Specifications

MODEL TEXT	
Key Benefit	Control up to 8 computers with a single KVM switch with integrated console. This KVM switch is a smart solution for secure and centralized server control that saves rack space and money.
OVERVIEW	



Users	1
Console	1
Max CPU	8
Shipping Weight	47.4 lbs.
INPUT	
Nominal Input Voltage(s) Supported	100V AC; 110V AC; 115V AC; 120V AC; 127V AC; 140V AC; 200V AC; 208V AC; 220V AC; 230V AC; 240V AC
Input Frequency	50/60Hz
Input Current	120V (0.8A) / 230V (0.4A)
PHYSICAL	
Unit Dimensions (hwd / in.)	1.75 x 16.75 x 24
Unit Dimensions (hwd / cm)	4.45 x 42.55 x 60.96
Color	Black
LCD Monitor (in.)	17
LCD Monitor (cm)	43.18
ENVIRONMENTAL	
Relative Humidity	0% TO 80% RH
Operating Temperature	32 DEGREES TO 120 DEGREES F
BTUs	76.1 BTUs at 120V, 50Hz or 83.98 BTUs at 230V, 50Hz
COMMUNICATIONS	
Port Control	Push Buttons, Hotkeys, OSD
IP Remote Access	0
CONNECTIONS	
Ports	8
Computer/Server Ports	(x8) HD15 (Female)
PC/Server Connections	PS/2
SPECIAL FEATURES	
Cat5 KVM Switch	0
CERTIFICATIONS	
Certifications	UL 60950-1 (USA), CAN/CSA (Canada), FCC Part 15 Class A, CE, IEC 60950-1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	1-year limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>