

## Heavy-Duty Power Cord, 15A, 14AWG (IEC-320-C19 to NEMA 5-15P), 10-ft.

MODEL NUMBER: **P034-010**



### Highlights

- C19 to 5-15P Power Cable, 10 ft.
- 14 AWG x 3C
- RoHS Compliant

### Package Includes

- C19 to 5-15P Power Cable, 10 ft.

### Description

Use Tripp Lite's P034-010 in server applications that require a higher rated, heavier gauge cable. IEC-60320-C19 to NEMA 5-15P connectors, 3 x 14 AWG conductors, 15A/125V rating.

### Features

- Molded, Heavy-Duty Power Cable, 10 ft.
- IEC-60320-C19 to NEMA 5-15P
- 14 AWG x 3C, SJT, 15A, 125 Volt
- RoHS Compliant

## Specifications

INPUT	
Cable Length (ft.)	10
Cable Length (m)	3.1
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	NEMA 5-15P
Side B - Connector 1	IEC-320-C19



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>