

In most applications, a signal booster (Model Number: B120-000) should be used with this cable to ensure a signal strong enough for your display. An alternate solution is to use a Tripp Lite DVI over Cat5 Extender (Model Number: B140-101X) in place of a 50 ft. DVI cable and signal booster. Note that Tripp Lite's DVI over Cat5 Extender products support DVI Single Link resolutions only.

DVI Dual Link Cable, Digital TMDS Monitor Cable (DVI-D M/M), 50-ft.

MODEL NUMBER: **P560-050**



Description

Tripp Lite's 50-ft. DVI Dual Link TMDS cable delivers the high performance, high bandwidth needed for today's digital video displays. Gold plated contacts ensure excellent conductivity, while double shielding (foil and braid) provides maximum EMI/RFI protection. Use in conjunction with DVI video cards that are specified as Dual or Single Link. Both DVI connectors are molded, have integral strain relief for long life reliability, and ferrite collars to drain off extraneous electrical interference. In most applications, a signal booster ([B120-000](#)) will need to be used with this cable to ensure a signal strong enough for your display.

Features

- For use with Dual or Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection
- In most applications, a signal booster ([B120-000](#)) will need to be used with this cable to ensure a signal strong enough for your display

Specifications

Highlights

- For use with Dual or Single Link TMDS specified equipment
- Compatible with Flat Panel Displays, Digital CRT Displays and Projectors
- Provides bandwidth for resolutions up to 2560 x 1600
- High Speed Digital Transmission to 9.9Gbps
- Superior molded cables with foil/braid shielding for maximum EMI/RFI protection

System Requirements

- DVI monitor
- CPU with DVI Dual Link capabilities

Package Includes

- 50-ft. DVI Dual Link TMDS Cable (DVI-D M/M)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

INPUT	
Cable Length (ft.)	50
Cable Length (m)	15.2
PHYSICAL	
Color	Black
CONNECTIONS	
Side A - Connector 1	DVI-D DUAL LINK (MALE)
Side B - Connector 1	DVI-D DUAL LINK (MALE)
CERTIFICATIONS	
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>