

Protect It! 8-Outlet Computer Surge Protector, 8-ft. Cord, 2160 Joules, Tel/Modem/Fax Protection

MODEL NUMBER: TLP808TEL



Highlights

- 8 outlets / 8-ft. cord
- 2160 joule rating
- Modem/fax surge protection
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Package Includes

- TLP808TEL
- 6-ft. telephone cord
- Instruction manual with warranty information

Description

Tripp Lite's TLP808TEL surge suppressor has 8 outlets, an 8-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2160 joules to handle the strongest surges. Built-in RJ11 jacks prevent surges from damaging your modem/fax/phone equipment. \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

Features

- 2160 joules AC surge suppression shields equipment from the strongest surges and line noise
- 8 AC outlets with room for 3 transformer plugs without blocking outlets covers computers and all peripherals
- Long 8 foot AC line cable with space-saving angle input plug conveniently reaches distant outlets
- built-in RJ11 jacks (1in/2 out) prevent surges from damaging your modem/fax/phone equipment
- Lighted power switch with integrated 15 amp circuit breaker offers power control and overload protection
- Integrated child-safety sliding outlet covers safely seal off all unused outlets
- Diagnostic LEDs confirm outlet grounding and surge suppression status
- Attractive white suppressor housing with keyhole mounting tabs allow versatile placement options
- \$150,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

OUTPUT



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) 5-15R
Output (Watts)	1800W
Circuit Breaker (amps)	15
Transformer Accommodation	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 6 transformers total
Outlet Safety Covers	Includes built-in sliding outlet safety covers
Outlet Orientation	Single row of 5, plus a second row of 3 for transformer accommodation
Right-Angle Outlets	0
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Plug Features	Space-saving right angle input plug
Input Cord Length (ft.)	8
Input Cord Length (m)	2.4
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
Maximum Surge Amps	144000
Right-Angle Plug	1
USER INTERFACE, ALERTS & CONTROLS	
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
SURGE / NOISE SUPPRESSION	
AC Suppression Joule Rating	2160
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	330/400/400
EMI / RFI Filtering	Up to 40 dB
DATALINE SURGE SUPPRESSION	
Telephone/DSL Protection	1



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Telephone/DSL Protection Details	1 line
Cable (Coax) Protection	0
Network (Ethernet) Protection	0
PHYSICAL	
Shipping Dimensions (hwd / in.)	11.41 x 8.66 x 2.04
Shipping Dimensions (hwd / cm)	28.98 x 22.00 x 5.18
Shipping Weight (lbs.)	2.06
Shipping Weight (kg)	0.93
Unit Dimensions (hwd / in.)	4.86 x 9.55 x 1.51
Unit Dimensions (hwd / cm)	12.34 x 24.26 x 3.84
Unit Weight (lbs.)	1.89
Unit Weight (kg)	0.86
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting slots enable wall mounting
Housing Color	Light Gray
Receptacle Color	Light Gray
Color (AC Line Cord)	Light Gray
Keyhole Slot Mounting Measurement (Center to Center)	Distance between horizontal slots = 75mm; Distance between vertical slots = 41.6mm
SPECIAL FEATURES	
Additional Information	Pair of phone line output jacks serve as a line splitter to enable the protection of two devices sharing a single dialup phone line
CERTIFICATIONS	
UL1449 3rd Edition (AC Suppression)	UL1449 3RD EDITION
UL1363 (Power Tap)	UL1363
UL497A (Communications)	UL497A
FCC Part 68 (Communications)	FCC Part 68
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$150,000 <u>Ultimate Lifetime Insurance</u>
---	--

© 2017 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:
<https://www.tripplite.com/products/product-certification-agencies>