# **Protect It! Surge Suppressor**

State of the art protection for every application



#### Model #: SUPER7

- 7 outlets/7 ft. cord
- 2350 joule rating

#### **DESCRIPTION**

The SUPER7 Surge Suppressor from Tripp Lite has 7 outlets, a 7-ft. cord with a space-saving right-angle plug, and diagnostic LEDs. The unit has a surge suppression rating of 2350 joules to handle the strongest surges. Ultimate Lifetime Insurance (USA & Canada Only).

#### **KEY BUYING POINTS**

- 7 outlets
- · 7-ft. cord with space-saving right-angle plug
- Surge suppression rating: 2350 joules
- EMI/RFI noise filtering
- Can accommodate up to 3 transformers without blocking remaining outlets
- Ultimate Lifetime Insurance (USA & Canada Only) covers connected equipment
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting
- · Lifetime product warranty

#### TYPICAL APPLICATIONS

Personal computers, CAD/CAM/CAE workstations, network nodes, fileservers, point-of-sale terminals, audio/visual devices, and more.

## **PACKAGE INCLUDES**

- Super 7 Surge Suppressor
- Instruction manual with warranty information

### **COMPLETE SPECIFICATIONS**

SYSTEM OVERVIEW	
System overview:	SUPER7 surge suppression strip includes 7 AC outlets, 7 foot AC cord, 2350 joule protection level, diagnostic LEDs, 3 dedicated transformer outlets, lifetime warranty and connected equipment insurance
Voltage compatibility:	120 VAC
Frequency compatibility:	50/60 Hz
OUTPUT	
Output volt amp capacity (amps):	15
Output watt capacity (watts):	1800
Outlet quantity / type:	7 NEMA 5-15R output receptacles

Outlet orientation:	Single row of 5, plus 2 side mounted outlets
Transformer accomodation:	Supports 3 large transformer plug accessories without covering remaining outlets, accepts up to 5 transformers total
INPUT	
Input connection type:	NEMA 5-15P
Input cord length (ft.):	7
Input cord length (m):	2.1
Input cord gauge, type:	14 gauge, SJT
Recommended electrical service:	120V 15A
LEDS ALARMS & SWITCHES	
Diagnostic LEDs:	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
Switches:	Two position on/off power switch
AC SURGE / NOISE SUPPRESSION	
Protection modes:	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
AC suppression joule rating:	2350 joules
Clamping voltage (RMS):	150V
AC suppression response time:	< 1 ns
UL1499 let through rating:	330V - UL Verified
EMI / RFI filtering:	Up to 20 dB
PHYSICAL	
Shipping weight (lbs):	1.6
Shipping weight (kg):	0.7
Unit weight (lbs):	1.4
Unit weight (kg):	0.6
Unit Dimensions (HWD/in):	10.25 x 2.75 x 1.5
Unit Dimensions (HWD/cm):	26 x 7 x 3.8
Shipping Dimensions (HWD/in):	13 x 5.25 x 1.9
Shipping Dimensions (HWD/cm):	33 x 13.3 x 4.8
Material of construction:	Plastic
Integrated keyhole mounting tabs:	Keyhole mounting tabs enable wall mounting
Housing color:	Attractive gray color scheme
AC line cord color:	Gray
CERTIFICATIONS	
UL1449 1998 Rev. (AC Suppression):	UL1449
UL1363 (Power Tap):	UL1363
cUL / CSA (Canada):	cUL
Approvals:	Exceeds IEEE 587 category A&B specifications
WARRANTY	
Product warranty:	Lifetime
Connected equipment insurance (USA and Canada Only):	

When you order today, you will receive the updated new version of these surge suppressors, however, they may be in packaging that still reflects the old specifications for joule and insurance amounts. In some cases the packaging you receive may have a sticker indicating these upgrades. This is simply due to an excess supply of existing packaging. Tripp Lite's ongoing commitment to having large quantities of product

in stock at all times requires us to maintain large quantities of packaging. We are using this supply up as quickly as possible and are in the process of transitioning to new packaging. The timing will vary by product.

Please bear with us during this period of transition and rest assured that Protect It! Surge Suppressors are among the finest surge protection products available. If you want to know if your Protect It! Surge Suppressor offers the latest joule ratings and/or insurance amounts, refer to the date code on the back of your unit. If it was manufactured after 1/7/02 it is an upgraded version. For additional questions feel free to contact our Technical support hotline at (773) 869-1234 or email techsupport@tripplite.com.

The policy of Tripp Lite is one of continuous improvement.

Specifications are subject to change without notice.

Therefore, your product may vary slightly from what is currently listed.



Tripp Lite World Headquarters 1111 W. 35th Street Chicago, IL 60609 USA

> Customer Support (773) 869-1234

© 2004 Tripp Lite. All Rights Reserved.