



AMPROBE®

AMB-25 & AMB-35

Digital Megohmmeters - Insulation Resistance Testers



Quality does not have to be expensive. These affordable megohmmeters still offer a solid range of features designed to meet most insulation test applications.

- Test insulation of wires, cables, transformers and motors
- Come as a complete kit including test leads
- Selectable test voltages up to 1000V
- Button Lock for Dielectric Absorption Ratio Test
- Sensitive Ohmmeter for checking resistance of motor windings
- Built in voltmeter (AMB-35 only)
- Internal memory (stores 9 readings)
- Fast and easy to use, rugged durable design



FEATURES	AMB-25	AMB-35	ACCURACY
Insulation resistance with 250, 500 & 1000 VDC test voltages	0 - 4.000 / 40.00 / 400.0 / 4000 MΩ	0 - 4.000 / 40.00 / 400.0 / 4000 MΩ	± 3% Rdg ± 5 LSD < 1GΩ ± 5% Rdg ± 5 LSD < 4GΩ
Resistance	0 - 9999Ω	0 - 9999Ω	1% Rdg ± 2 LSD
Low Resistance		0.10 - 40.00Ω	2% Rdg ± 2 LSD
AC/DC Voltage		0.1 - 1000.0V	± 2.0% Rdg ± 1 LSD

REPLACEMENT PARTS <small>(supplied with product)</small>	PART NUMBER
Test leads complete set	MTL-45
Instruction Manual	

OPTIONAL ACCESSORIES	PART NUMBER
Carrying case	GP-2CC

