

50 Watt Alpha Halogen 30" Reach Magnetic Mount



Model: 7330
Magnetic Base



Model: 7332
Clamp on



Model: 7333
Direct Base

- These powerful 50 watt halogen lamps combined with anodized reflectors produce a concentrated, evenly-spread, brilliant white light over work surfaces.
- The compact 3" x 4" moisture-resistant metal shade and on/off switch are sealed to protect against dust and moisture.
- The sturdy flexible gooseneck with an overall 30" reach, adjusts to direct light where needed.
- Mounting options include clamp-on, for surfaces up to 1 3/4" thick, 90lb pull magnetic base or direct mounting base with hardware.
- Rated NEMA 13, this light comes complete with bulb and 7 ft cord with plug-in transformer. 3 year warranty. Made in USA.