

## 55 Watt 27" Gooseneck Halogen Machinist Lamp



- 27" flexible reach
- 9.5 ft grounded SJTO power cord & plug
- 55 watt Halogen bulb
- 12 volt integrated transformer
- Rubber boot switch on shade
- Safe, low voltage

### Model: 7712

This rugged, all metal construction, waterproof machine task light provides excellent illumination in touch and wet locations. Engineered to deliver intensified, bright white Halogen light to meet the needs of demanding shop environments, it features safe, low voltage, 55w/12v power. This light meets NEMA Type 4 certification (hose down, icing and gaskets application), which makes it ideal for CNC and EDM wet location machinery, lathes, milling, metal-working and tool manufacturing. Added safety features include a rubber boot switch, sealed from liquids, a 9 ft grounded, oil and water resistant SJTO cord with 3-prong plug, and integrated transformer housed in a liquid tight precision cast zinc base housing. The heavy gauge aluminum shade is precision machined to fit a vented inner chamber which eliminates heat build-up, providing added comfort to the operator while maintaining water tight features. With its 26" industrial grade steel gooseneck, this lamp will flex and maintain any position. 3 year warranty. Made in USA. Available Colors: Black