

MR-16 Halogen 25" Reach Portable Desk Lamp



- 25" flexible reach
- 3" x 3" compact shade
- On/Off Switch
- 20 Watt MR-16 Halogen bulb
- Glass UVB filter enclosure
- 7" diameter tip resistant base
- 9 ft grounded 3-prong plug and cord

Model: 6000

This personal, portable and yet powerful desk lamp features a 25 inch flexible gooseneck arm constructed of tough and durable, heavy-duty steel sheathed inside an elegant poly-vinyl coating. Excellent as a computer workstation light, it flexes to concentrate a crisp, bright white light onto paperwork without glare on the computer screen while the sturdy arm resists drooping and sagging. The 12 volt transformer is safely housed in the tip resistant lamp base and the 20 watt Halogen bulb, included, is enclosed inside a glass UVB filter surrounded by a compact 3" x 3" metal shade. 3 year warranty. Made in USA. UL & CSA Listed.