



Part Number	PG	NPT	D	D1	D2	L	L1	L2	L3	SW
73 00 000 5308	PG11	3/8	24.0	14.0	21.0	19.0	10.0	6.0	7.0	22.0
73 00 000 5310	PG11	1/2	29.0	15.0	25.0	20.5	11.5	6.0	9.5	27.0
73 00 000 5311	PG13	1/2	29.0	17.8	25.0	22.5	11.5	8.0	9.5	27.0
73 00 000 5312	PG16	1/2	29.0	17.8	25.0	22.5	11.5	8.0	9.5	27.0
73 00 000 5313	PG21	1/2	35.5	18.5	30.0	23.0	12.0	8.0	9.5	32.0
73 00 000 5314	PG21	3/4	35.5	23.0	30.0	25.0	12.0	10.0	10.0	32.0
73 00 000 5315	PG29	1	43.5	29.0	38.0	30.0	17.0	10.0	14.0	40.0
73 00 000 5316	PG29	1 1/4	55.6	32.0	47.5	32.0	17.5	10.0	16.0	50.0
73 00 000 5317	PG36	1 1/4	54.0	37.8	48.0	31.0	17.5	10.0	15.0	50.0
73 00 000 5346	PG42	1 1/2	60.0	43.8	56.0	32.0	18.5	10.0	15.0	57.0

<p>All Dimensions in mm Original Size DIN A 4</p>	Techn. Character			Free size tolerances												
	<table border="1"> <tr> <td>Detail</td> <td>Dat.</td> <td>Name</td> <td>Scale</td> </tr> <tr> <td>Insp.</td> <td></td> <td></td> <td></td> </tr> <tr> <td>Stand.</td> <td></td> <td></td> <td></td> </tr> </table>	Detail	Dat.	Name	Scale	Insp.				Stand.				<p style="text-align: center;"><b>Adapters</b> From PG to NPT</p> <p style="text-align: center;"><b>Nickel Plated Brass</b></p>		
Detail	Dat.	Name	Scale													
Insp.																
Stand.																
<table border="1"> <tr> <td>Mod.</td> <td>Dat.</td> <td>Name</td> </tr> <tr> <td></td> <td></td> <td></td> </tr> </table>	Mod.	Dat.	Name				HARTING INC. OF NORTH AMERICA 1370 BOWES ROAD ELGIN, IL 60123 PH: (847)741-1500			Sub.						
Mod.	Dat.	Name														