



## Ethernet Switch Ha-VIS eCon 3062-AE

8-port Ethernet Switch for vertical installation in control cabinets,  
including 2 F.O. ports (ST, MM)

Unmanaged	IP 30	PROFINET compatible <input checked="" type="checkbox"/>	EtherNet/IP compatible <input checked="" type="checkbox"/>
Number of ports, Copper / Termination	6x 10/100Base-T(X) / RJ45 (Twisted Pair)		
Number of ports, F.O. / Termination	2x 100Base-FX / ST female		
Input voltage / Termination	24 V DC / 3-pole, pluggable screw contact (24 V, 0, FE)		
Permissible range (min./max.)	9.6 V ... 60 V DC		
Input current	approx. 240 mA (at 24 V DC)		
Housing material	metal, powder-coated		
Dimensions (W x H x D)	23 x 130 x 100 mm (without connectors)		
Weight	approx. 0.6 kg		
Working temperature	-10 °C ... +70 °C		
Approvals	UL 508		
MTBF	825.000 h		

Identification	Part number	Drawing	Dimensions in mm
Ha-VIS eCon 3062-AE Ethernet Switch with 6 RJ45 ports 2 F.O. ports	20 76 108 3200		