

RG160AC Series

Flatpak

220x220x56mm



- AC radial blower with external rotor shaded-pole motor. Impedance protected against overloading.
- Radial air exhaust through housing port. Rotational direction CCW looking at rotor.
- Spiral housing and blower of fiber-glass reinforced plastic. Housing base of galvanised steel plate.
- Electrical connection via leads AWG 18. Stripped and tinned ends.
- UL, CSA, VDE approvals on some models, please contact application engineering.

Part Number	Curve	CFM @ 0	VAC	Hertz	Power (W)	dBA	Max Amb. Temp C	Bearing Type	Features	Wgt. (lbs)
RG160-28/56S	1	118.9	230	50	47	69	70	Ball	Leads	3.31
RG160-28/06S	2	131.3	115	60	50	69	80	Ball	Leads	3.31

