
Mini I/O, 12 Position XX-9257





AVX offers the 12 way mini I/O connector as a standard product. The fixed SMT socket is designed to be mounted on a PCB and housed within a portable device. The plug is designed for cable termination with options of single and double sided contacts. Parts can be supplied as connectors only for sub contract termination, or with a custom overmold cover. The socket connector houses 12 contacts in a single row on 0.50mm pitch.

APPLICATIONS

- Medical Electronics
- Cellular Phones
- Industrial Modules
- Hand Held Devices

FEATURES AND BENEFITS

- No latching required due to the click design of the contacts.
- Optional customization of the overmold cover.
- Compact size to optimize PCB real estate.
- Metal outer cover provides integrated PCB location and solder tab.
- Positive alignment and orientation of the plug and socket.

RoHS

COMPLIANT

ELECTRICAL

- Current Rating: 0.5 Amp / Contact
- Voltage Rating: 50 VAC

ENVIRONMENTAL


• Operating Temperature: -55°C to +85°C


MECHANICAL

- Insulator Material: High Temperature Plastic; • UL94 V-O
- Contact Material: Phosphor Bronze (Plug) • Copper Alloy (Socket) •
- Plating: Gold over Nickel
- Durability: 5,000 Cycles

HOW TO ORDER

Plug Options







Certification: UL File #E90723



9257 STANDARD 12 WAY MINI I/O PLUG








5. PACKED IN TUBES, 60 PIECES PER TUBE.

PACKING DETAILS 60 PARTS PER TUBE






SUGGESTED OVERMOULDING FOR PLUG CONNECTOR








NOTES: DIMENSIONS MARKED WITH A * ARE VARIABLE DIMENSIONS TO SUIT CUSTOMER DESIGN AND APPLICATION

Mini I/O, 12 Position xx-9257



9257 STANDARD 12 WAY MINI I/O SOCKET



PACKING DETAILS

NOTES:

- 1. ALL DIMENSIONS SHOWN ARE REFERENCE DIMENSIONS UNLESS TOLERANCED.
- 2. FOR FULL PRODUCT SPECIFICATION REFER TO ELCO SPECIFICATION 201-01-116.
- 3. MATERIALS: INSULATOR: HIGH TEMP PLASTIC, UL94 V-O, COLOR BLACK. CONTACT: COPPER ALLOY. SHELL: STAINLESS STEEL.
- 4. PLATING: CONTACT: GOLD OVER NICKEL. SHELL: GOLD OVER NICKEL.
- 5. PACKED IN TAPE AND REEL, 1200 PIECES PER REEL.



| | | EQUAL SPACES @ 0.50 = 5.50