


PART NUMBER	82453	REV.	A
SHEET 2 OF 2			
DESCRIPTION OF CHANGE			
APPD.	REV.	DATE	PCN NO.
	A	21Jan02	32936
BY DDC			
RELEASED FOR PRODUCTION			

CUSTOMER: _____
 APPROVED BY: _____
 DATE: _____
 CUSTOMER PART NO.: _____

.150 DIA 3- HOLES EQL.SPACED
 DN 2.531 DIA. B.C.
 .125 DIA 3- HOLES EQL.SPACED
 DN 2.420 DIA. B.C.
 BACKGROUND BLACK WITH WHITE LETTERING

HOBBS CORP., PART NO., VOLTAGE, DATE CODE, POLARITY SENSITIVE, UL RECOGNIZED SYMBOL WITH (FILE NO) AU1774 & CSA SYMBOL WITH (FILE NO) LR42455 TO BE PRINTED ON LABEL.



- NOTES:
1. DATE CODE IS A 5 DIGIT NO, 1ST & 2ND DIGITS REPRESENT THE YEAR, THE NEXT 3 DIGITS REPRESENT THE DAY. EXAMPLE: 02285 IS 285TH DAY OF 2002
 2. METER REQUIRES A 2.00 DIA MOUNTING HOLE.
 3. OPERATING RANGE: 10 VDC (MIN) THRU 80 VDC (MAX).
 4. METER MUST BE MOISTURE RESISTANT WHEN SUBMERGED IN WATER AT +150 DEGREES F. FOR 3 MINUTES.

SIM. TD: 85000

CUSTOMER PRINT

DRAWN		CHECKED		MATERIAL		NAME	
DDC		SCALE		FINISH		DIDCHRON HOURMETER	
DATE		SCALE		PROPERTY OF HOBBS CORPORATION.		12-60 VDC SYSTEM 10,000 HRS	
18Jan02		1:1		DIMENSIONS ARE FOR REFERENCE		(2.8 DIA - 3 HOLE MOUNT)	
DID NOT SCALE		DKT. NO.		ONLY UNLESS OTHERWISE SPECIFIED.		NEXT ASSY.	
		01-182				PART NUMBER	
						82453	
						SHEET 2 OF 2	

J.W. HOBBS CORP. SPRINGFIELD, IL U.S.A.

PROPRIETARY INFORMATION.
 PROPERTY OF HOBBS CORPORATION.
 DIMENSIONS ARE FOR REFERENCE
 ONLY UNLESS OTHERWISE SPECIFIED.