Hobbs DC Hour Meters

85000 Series Quartz Plus DC Hour Meters




Round Chrome Bezel						
Operating Voltage	Part # Flush Cup 2.27"	Part # Flush Cup 2.50"	Part # Stirrup 2.27"	Part # Stirrup 2.50"		
10-32 VDC	85002	85006	85004	85008		
10-80 VDC	85342	85098				
30-110 VDC	85015	85019	85017	85021		




Round Black Bezel						
Operating Voltage	Part # Flush Cup 2.27"	Part # Flush Cup 2.50"	Part # Stirrup 2.27"	Part # Stirrup 2.50"		
10-32 VDC	85003	85007	85005	85009		
10-80 VDC	85093	85099				
30-110 VDC	85016	85020	85018	85022		

DC APPLICATIONS


- Lawn Tractors
- Garden Tractors
- · Farm Equipment
- · Gen Sets
- Construction
- Equipment
- · Utility Vehicles
- Industrial Equipment
- Recreational Vehicles
- · Golf Carts
- Aircraft
- Medical Equipment
- Office Equipment
- Any application requiring a very accurate and dependable hour meter.




Chrome Flush Mount (Cup) 2.27": Panel cutout 2.00 diameter opening. *



Chrome Flush Mount (Cup) 2.5": Panel cutout 2.00 diameter opening.*




Black Flush Mount (Stirrup) 2.27": Panel cutout 2.00 diameter opening.*



Black Flush Mount (Stirrup) 2.5": Panel cutout 2.00 diameter opening.*

^{*} Panel cutout dimensions are \pm .010 tolerance All dimensions shown in inches and (metric)



CAUTION: Always make sure power is removed from equipment before working on electrical circuits! Only qualified personnel should make electrical connections. Damage to equipment and/or serious bodily injury can result from improperly made electrical connections, or a failure to adhere to normal electrical safety guidelines