



Government Solutions

Market

- + Defense
- Energy
- Green Solutions
- Health Safety
- Homeland Security

Contracts

- General Services Administration
- Veterans Affairs

Product Information

- Government Catalogs
- Online Product Catalog
- FEDSPEC Locator
- NSN Locator

News

- Industry Links

Contact Information

- Contact Us



[Product Catalog for Government Solutions](#) > [Telecommunications / Network Products](#) > [Related Products](#) > [Tape](#) >

3M™ Antistatic Utility Tape, 40, 3/4 in x 36 yd (19.05 mm x 33 m)



[Click to Enlarge](#)

2.2 mil Clear Polyester Film Antistatic Utility Tape with a clear, one mil polyester film backing for use in static-sensitive areas.

Where To Buy

[Where to Buy](#)

Quick Links

- [Contact Us](#)
- [Material Safety Data Sheets \(MSDS\)](#)
- [OH&ES Distributor Login](#)
- [Industrial Distributor Login](#)

[Additional Information](#) [Documents](#) [Packaging](#)

3M Antistatic Utility Tape 40 combines 3M's remarkable antistatic adhesive with a clear, one mil polyester film backing, and is perfect for use in static-sensitive areas. An optional special pattern of ESD symbols alerts users that this is the only tape t

3M ID: 80-6108-4181-1

GTIN(UPC/EAN): 0 00 51138 46505 6

Characteristics:

Name	Value
Adhesive Type	Conductive Polymer
Backing Material	Antistatic
China RoHS - Below MCV	Yes
EU RoHS Compliant	Yes
Material	Polyester

Maximum Operating Temperature (Celsius)	130 Degree Celsius
Product Type	Anti-Static Utility Tape
Size	0.75 in. x 36 yd. (9.0 mm x 33 m)
Tape Length	36 Linear Yard
Tape Thickness	2.2 Milli-inch (mil)
Tape Total Thickness (metric)	0.056 mm
Tape Type	Anti-Static Utility
Tape Width	0.75 in
Tape Width (metric)	1.9 cm
Thickness	2.2 Milli-inch (mil)

