



**Government Solutions**

**Market**

- + Defense
- Energy
- Green Solutions
- Health Safety
- Homeland Security

**Contracts**

- General Services Administration
- Veterans Affairs

**Product Information**

- Government Catalogs
- Online Product Catalog
- FEDSPEC Locator
- NSN Locator

**News**

- Industry Links

**Contact Information**

- Contact Us



[Product Catalog for Government Solutions](#) > [Telecommunications / Network Products](#) > [Related Products](#) > [Tape](#) >

## 3M™ Antistatic Utility Tape, 40PR, 1/2 in x 72 yd (12.70 mm x 66 m)



[Click to Enlarge](#)

2.2 mil Clear Polyester Film Antistatic Utility Tape with a clear, one mil polyester film backing for use in static-sensitive areas.

**Where To Buy**

[Where to Buy](#)

**Quick Links**

- [Contact Us](#)
- [Material Safety Data Sheets \(MSDS\)](#)
- [OH&ES Distributor Login](#)
- [Industrial Distributor Login](#)

[Additional Information](#)   [Documents](#)   [Packaging](#)

3M Antistatic Utility Tape 40 combines 3M's remarkable antistatic adhesive with a clear, one mil polyester film backing, and is perfect for use in static-sensitive areas. An optional special pattern of ESD symbols alerts users that this is the only tape t

**3M ID:** 80-6108-7260-0

**GTIN(UPC/EAN):** 0 00 51138 47774 5

**Characteristics:**

Name	Value
Adhesive Type	Conductive Polymer
Backing Material	Antistatic
China RoHS - Below MCV	Yes
EU RoHS Compliant	Yes
Material	Polyester

Maximum Operating Temperature (Celsius)	130 Degree Celsius
Product Type	Anti-Static Utility Tape
Size	0.50 in. x 72 yd. (12.6 mm x 66 m)
Tape Length	72 Linear Yard
Tape Thickness	2.2 Milli-inch (mil)
Tape Total Thickness (metric)	0.056 mm
Tape Type	Anti-Static Utility
Tape Width	0.50 in
Tape Width (metric)	1.2 cm
Thickness	2.2 Milli-inch (mil)

