

United States [ Change]

## **Electrical OEM Materials**

Products

Overview

**Documentation & Literature** 

**News & Tradeshows** Support

<u>United States > All 3M Products > Market Segments > Electronics, Electrical, and Communications</u> > <u>Electrical Products > Electrical OEM</u> <u>Materials > Products</u> > <u>Electrical OEM Products Catalog</u> > <u>Electrical & EMI Tapes</u> > <u>Tapes</u> > <u>3M™</u> Antistatic Utility Tape, 40PR, 1/2 in x 72 yd (12.70 mm x 66 m)

Find An Account Rep (Where To Buy) Contact Us

## 3M<sup>™</sup> Antistatic Utility Tape, 40PR, 1/2 in x 72 yd (12.70 mm x 66 m)

3M ID 80610872600 UPC# 00051138477745 3M Product Number 40PR 1/2X72 3M Product Number 40PR-1/2"X72YD



Documentation

## Content blocked by your

2.2 mil Clear Polyester Film Antistatic Utility Tape with a clear, one mil polyester film backing for use in static-sensitive areas. **Need Help?** 

Questions? We can help Contact Us

Specifications
Adhesive Type Conductive Polymer
Backing Material Antistatic
China RoHS - Below MCV Yes
EU RoHS Compliant Yes
Material Polyester
Maximum Operating Temperature (Celsius) 130 Degree Celsius
Product Type Anti-Static Utility Tape
<b>Size</b> 0.50 in. x 72 yd. (12.6 mm x 66 m)
Tape Length 72 Linear Yard
Tape Thickness2.2 Milli-inch (mil)
Tape Total Thickness (metric)0.056 mm
Tape Type Anti-Static Utility
Tape Width0.50 in
Tape Width (metric)1.2 cm
Thickness 2.2 Milli-inch (mil)

• Print

Q