



Electrical OEM Materials

- Products
- Documentation & Literature
- News & Tradeshow
- Support

United States > All 3M Products > Market Segments > Electronics, Electrical, and Communications > Electrical Products > Electrical OEM Materials > Products > Electrical OEM Products Catalog > Electrical & EMI Tapes > Tapes > 3M™ Antistatic Utility Tape, 40, 1/2 in x 72 yd (12.70 mm x 66 m)

Find An Account Rep (Where To Buy)

Contact Us

3M™ Antistatic Utility Tape, 40, 1/2 in x 72 yd (12.70 mm x 66 m)

3M ID 80610872683    UPC# 00051138477820    3M Product Number 40 1/2X72    3M Product Number 40-1/2"X72YD

• [Print](#)



Content blocked by your

2.2 mil Clear Polyester Film Antistatic Utility Tape with a clear, one mil polyester film backing for use in static-sensitive areas.

Need Help?

Questions? We can help

Contact Us

- Overview
- Documentation

Specifications

Adhesion Strength	15 Ounce
Adhesive Material	Acrylic
Adhesive Type	Conductive Polymer
Backing Material	Antistatic
Breaking Strength	20 Pound Per Inch (Of Width)
China RoHS - Below MCV	Yes
Core Material	Plastic
Core Size	3 Inch
EU RoHS Compliant	Yes
Flammability Rating--USA	None
Insulation Resistance	1 x 10^6 megohms
Material	Polyester
Maximum Operating Temperature (Celsius)	130 Degree Celsius
Product Type	Anti-Static Utility Tape
Size	0.50 in. x 72 yd. (12.6 mm x 66 m)

<b>Tape Length</b>	72 Linear Yard
<b>Tape Thickness</b>	2.2 Milli-inch (mil)
<b>Tape Total Thickness (metric)</b>	0.056 mm
<b>Tape Type</b>	Anti-Static Utility
<b>Tape Width</b>	0.50 in
<b>Tape Width (metric)</b>	1.2 cm
<b>Thickness</b>	2.2 Milli-inch (mil)
<b>Width</b>	1/2 Inch

**3M OEM Electrical:** [Contact Us](#)

**3M:** [News](#) | [Careers](#) | [Investor Relations](#) | [MSDS Search](#) | [Transport Information Search](#) | [A-Z Product Index](#) | [Contact 3M](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2013. All Rights Reserved.

