

[All 3M Products](#) [Newsroom](#) [About 3M](#)Search 

United States [Change]

[United States](#) > [Government Solutions](#) > [All 3M Products](#) > [Industry and Professionals](#) > [Electronics & Electrical Supplies](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Safety and Protection Products](#) > [Respirators](#) > [3M™ Cartridge/Filter](#) > 3M™ Multi Gas/Vapor Cartridge/Filter 60926, P100 Respiratory Protection 60 EA/Case

3M™ Multi Gas/Vapor Cartridge/Filter 60926, P100 Respiratory Protection 60 EA/Case

3M ID 70070709483 UPC# 50051138541878 3M Product Number 60926 CAT# 60926



NIOSH approved against certain organic vapors, acid gases and particulates. Use with 3M™ Half and Full Facepieces 6000, 7000 and FF-400 Series with bayonet filter holders.

- NIOSH approved for protection against certain organic vapors, acid gases, ammonia, methylamine, formaldehyde and particulates
- Swept-back design allows an enhanced field of view and comfort
- Bayonet compatibility allows use with many 3M half and full facepiece designs
- Wide range of applications reduces inventory needs
- Simple installation and usage requirements reduce training needs

[Print](#)**Need Help?**[Share](#)**Questions?** We can help
[Contact Us](#)[Buy at Shop3M.com](#)[Where to Buy](#)**Overview****Documents**

The 3M™ Multi Gas/Vapor Cartridge/Filter 60926 P100 may be used for respiratory protection from certain organic vapors, chlorine, hydrogen chloride, sulfur dioxide, chlorine dioxide, hydrogen sulfide, ammonia, methylamine, formaldehyde, or hydrogen fluoride, and non-oil and oil particulate concentrations up to 10 times the Permissible Exposure Limit (PEL) with half facepieces or 50 times PEL with quantitatively fit tested full facepiece masks. This cartridge/filter is not for use in environments that are immediately dangerous to life or health (IDLH). Recommended applications for the cartridge/filter include petrochemical and chemical processing. Inventory needs and training requirements for safety equipment are reduced because this respirator cartridge selection works for many different applications. This cartridge/filter is commonly used in the following industries: utilities, pharmaceuticals, mining, and primary metals.

This multi gas/vapor cartridge/filter combination works with 3M™ Half and Full Facepieces 6000, 7000 and FF-400 Series with bayonet attachment holders. The cartridge/filter is NIOSH (National Institute for Occupational Safety and Health) approved for environments containing certain organic vapors, acid gases, ammonia, methylamine, formaldehyde and non-oil and oil particulates. The cartridge/filter has been assigned the color code "Magenta/ Olive" in the NIOSH system.

Breathing organic vapors, acid gases, ammonia, methylamine, formaldehyde and particulates can pose a risk to your health. NIOSH, a Federal government regulatory agency, has tested and approved the 3M™ Multi Gas Vapor Cartridge 60926 to help reduce exposure to certain organic vapors, acid gases, ammonia, methylamine, formaldehyde and particulates.

Specifications

Connection Type	Bayonet
Features	Particulate filter permanently attached to cartridge
Gas & Vapor Protection Type	Organic Vapor/Acid Gas/Ammonia/Methylamine/Formaldehyde
Height	3.4 Inch
Length	4.2 Inch
National Stock Number	4240-01-455-7370
NIOSH Cartridge or Filter Assigned Color Coding	Magenta/Olive
Nuisance Odor Relief (< OSHA PEL)	N/A
Product Series	Half Facepiece Rugged Comfort 6500 Series

Recommended Industry	Construction, General Manufacturing, Mining, Oil & Gas
Standards/Approvals	Ammonia, Chlorine, Chlorine dioxide, Formaldehyde, Hydrogen chloride, Hydrogen Fluoride, Hydrogen sulfide, Methylamine, Organic Vapors, P100, Sulfur dioxide
US Govt Contract Number	GS-07F-0374J

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2015. All Rights Reserved.