



Electrical Commercial and Industrial

Products | Documentation & Literature | News & Tradeshows | Support

[United States](#) > [All 3M Products](#) > [Electronics](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Terminals, Kits and Tools](#) > [Terminals](#) > 3M™ Scotchlok™ Butt Connector Seamless Vinyl Insulated, 50/bottle, MV10BCX

3M™ Scotchlok™ Butt Connector Seamless Vinyl Insulated, 50/bottle, MV10BCX

3M ID 80611464134 UPC# 0005112858766 Part Number MV10BCX

Butt Connector Seamless Vinyl Insulated, 50/bottle, MV10BCX



Overview

Documents

Specifications

Agency Approvals	UL and CSA
Barrel Length	0.38 Inch
Barrel Style	Seamless
Brand	Scotchlok
Conductor Sizes	12 - 10 AWG
CSA File Number	LR22190
Insulation Material	Vinyl
Length	1.2 Inch
Maximum Insulation Outer Diameter	0.218 Inch
Packaging	50 per bottle
RoHS 2011/65/EU Compliant	Yes
Terminal Style	Standard
Terminal Type	Butt
Thickness	0.038 Inch
Trademark	Scotchlok
UL File Number	E23438

Manufacturing Origin: USA

The designation that a product is Manufactured in the USA means the product undergoes substantial transformation in one of our U.S. Manufacturing plants. Some products contain imported components.

Note: 3M products offered on a government contract that require country of origin representation must be certified by 3M Trade Compliance. Contact customer service at 800-245-3573 to request a certificate.