



Search This Product Catalog

[Product Catalog for Global Telecommunications OEM Site](#) > [Products for Carriers](#) > [Related Products](#) > [Tape](#) >

 **Printer-friendly format 3M™ Temflex™ 1755 Cotton Friction Tape, Black, 3/4 in x 60 ft (19 mm x 18,3 m), 60 per case**



[\[click to enlarge\]](#)

This black 15 mil friction tape offers good abrasion resistance up to 176°F (80°C). Packed in bulk with 60 rolls per case. This tape is a high grade cotton friction tape to provide abrasion protection in wire and cable splices as well as an overwrap for mechanical protection.

3M Id : 80-6107-3790-2  
GTIN(UPC/EAN) : 0 00 54007 50218 0

**Additional Information**

**Learn More . . .**

[Packaging Data](#)

[MSDS \(United States\)](#)

[1755 Cotton Friction Tape - Data Sheet \(PDF 8.2 K\)](#)

**Please Note:**

Adobe® Acrobat® Reader is required to view PDF documents.



**Characteristics**

<b>Adhesive Material</b>	Thermosetable rubber resin
<b>Backing Material</b>	Cotton Cloth
<b>Breaking Strength</b>	40 Pound Per Inch (Of Width)
<b>Color</b>	Black
<b>Core Material</b>	Paper
<b>Core Size</b>	3 Inch
<b>Length</b>	60 Linear Foot
<b>Maximum Operating Temperature</b>	80 Degree Celsius
<b>Primary Trademark Name</b>	Scotch
<b>Thickness</b>	15 Milli-inch (Mil)
<b>Width</b>	3/4 Inch

- Return to Solutions for Network Equipment Manufacturers
  - Product Catalog for Global Telecommunications OEM Site
    - Products for Business Enterprise
    - Products for Carriers
    - Products for Equipment Manufacturers

- Related Solution Sites
  - 3M Access Network
  - Enterprise Networks