



Electrical Commercial and Industrial

[Products](#) | [Documentation & Literature](#) | [News & Tradeshow](#) | [Support](#)

[United States](#) > [Energy](#) > [Electrical Commercial and Industrial](#) > [Products](#) > [Electrical Commercial & Industrial Products Catalog](#) > [Electrical Wire Connectors and Tools](#) > [Spring Connectors and Tools](#) > 3M™ Highland™ Wire Connector H-29-BOX, Gray, 22-16 AWG, 100 per Box

[Find An Account Rep](#)

[Where To Buy \(Find A Distributor\)](#)

[Contact Us](#)

3M™ Highland™ Wire Connector H-29-BOX, Gray, 22-16 AWG, 100 per Box

3M ID 80610981229 UPC# 00054007431336 Part Number H-29-BOX

[Print](#)



3M™ Highland™ Wire Connectors make it quick and easy to match the right connector to the size of the wire. The shells are designed to withstand temperatures up to 221(deg)F (105(deg)C).

- Use the H-29 in pigtail applications where you need to connect and insulate 2 or more copper wires
- The straight, twist-on style connector is gray in color and provides a quick connection every time
- Works great for all kinds of jobs - from industrial and residential construction, to automotive, marine and appliance applications
- It's easy to spin and tighten the vinyl connector with its steel spring mechanism
- Use with copper conductors ranging from 22 to 16 AWG in size
- Operates well in temperatures up to 221 degrees F (105 degrees C)
- Use in 300V-rated applications
- UL Listed, CSA Certified and RoHS 2011/65/EU Compliant
- Connectors come 100/box or 1000/case

Need Help?

Questions? We can help
[Contact Us](#)

[Buy at Shop3M.com](#)

Overview

Documents

The 3M™ Highland™ Wire Connector H-29 does more than fit your application; it also fits your hand and feels good to use. This straight connector is made to last so you know you'll always have a strong electrical connection. The key to its power is the spring inside the connector. Made of steel with a non-corrosive coating, the spring can hold a number of 22 to 16 AWG solid or stranded copper wires securely. Built for harsh environments, the H-29 can really stand up to high temperatures. All our Highland connectors feature a color-coded shell, so you'll always know you're using the right connector for the right job. This product is UL Listed, CSA Certified and RoHS 2011/65/EU Compliant.

Specifications

Agency Approvals	UL and CSA
Brand	Highland
Color	Gray
Conductor Sizes	22 - 16 AWG
Connection Type	Wire
Connector Style	Twist On
Family	3M™ Highland™ Wire Connector
Flame Retardant	No
Maximum Recommended	300 V

Voltage Rating	
Maximum Wire Gauge	16 AWG
Minimum Wire Gauge	22 AWG
Packaging	Box
Product Family	3M™ Highland™ Wire Connector
Product Type	Connector
RoHS 2011/65/EU Compliant	Yes
RoHS EU Comments	RoHS 2011/65/EU compliant without exemption *Important RoHS information
Trademark	Highland

3M: [News](#) | [Careers](#) | [Partners & Suppliers](#) | [Investor Relations](#) | [SDS Search](#) | [Transport Information Search](#) | [Help Center](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2016. All Rights Reserved.