

A Electrical Commercial and Industrial

Scotch® Vinyl Electrical Color Coding Tape 35-Brown-3/4, 3/4 in x 66 ft (19 mm x 20,1 m), 100 per case

UPC# 00054007108856 3M Product Number 35-BROWN-3/4 3M ID 80610833941

This brown, 7 mil premium grade electrical vinyl tape stretches to conform to virtually any shape that requires color-coded insulation. Inner pack of 1 per canister, 10 per carton with 100 rolls per case.



Overview Support

Scotch® Vinyl Electrical Color Coding Tape 35 is used in phase identification, color coding leads and piping systems and for marking safety areas. This tape is abrasion- and weather-resistant, with excellent mechanical and electrical insulation properti

Specifications	
Adhesive Material	Rubber Resin
Agency Approvals	UL Listed, CSA Certified, VDE 0340-TEIL1
Backing Material	Polyvinyl Chloride
China RoHS - Below MCV	Yes
Dielectric Strength	1250 Millivolt
EU RoHS Compliant	Yes
Length	66 Linear Foot
Maximum Operating Temperature (Celsius)	105 Degree Celsius
Operating Temperature Range	0 to 105 Degree Celsius
Product Family	Scotch® Vinyl Color Coding Electrical Tape 35
Product Type	Vinyl Tape
Tape Color	Brown
Tape Grade	Professional
Tape Length	66 Linear Foot
Tape Total Thickness	7 Milli-inch
Tape Total Thickness (metric)	0.177 mm
Таре Туре	Vinyl Electrical
Tape Width	0.75 in
Thickness	7 Milli-inch (mil)
Width	3/4 Inch