



# Scotch® Vinyl Electrical Color Coding Tape 35-Orange-1/2, 1/2 in x 20 ft (13 mm x 6,1 m), 100 per case

UPC# 00054007102731 3M Product Number 35-ORANGE-1/2 3M ID 80610834014



This orange, 7 mil premium grade electrical vinyl tape stretches to conform to virtually any shape that requires color-coded insulation. Inner pack of 1 per sleeve, 10 per carton with 100 rolls per case.

## Overview

Scotch® Vinyl Electrical Color Coding Tape 35 is used in phase identification, color coding leads and piping systems and for marking safety areas. This tape is abrasion- and weather-resistant, with excellent mechanical and electrical insulation properties.

## Specifications

<b>Adhesive Material</b>	Rubber Resin
<b>Agency Approvals</b>	UL Listed; CSA; VDE 0340-TEIL1
<b>Backing Material</b>	Polyvinyl Chloride
<b>Breaking Strength</b>	17 Pound Per Inch (Of Width)
<b>China RoHS - Below MCV</b>	Yes
<b>Color</b>	Orange
<b>Dielectric Strength (V/mil)</b>	1250 V/mil
<b>EU RoHS Compliant</b>	Yes
<b>Length</b>	20 Linear Foot
<b>Maximum Operating Temperature (Celsius)</b>	105 Degree Celsius
<b>Operating Temperature Range</b>	0 to 105 Degree Celsius
<b>Product</b>	Scotch® Vinyl Electrical Tape 35
<b>Product Family</b>	Scotch® Vinyl Color Coding Electrical Tape 35
<b>Product Type</b>	Vinyl Tape
<b>Tape Color</b>	Orange
<b>Tape Grade</b>	Professional
<b>Tape Length</b>	20 Linear Foot
<b>Tape Total Thickness</b>	7 Milli-inch
<b>Tape Total Thickness (metric)</b>	0.177 mm
<b>Tape Type</b>	Vinyl Electrical
<b>Tape Width</b>	0.50 in
<b>Thickness</b>	7 Milli-inch (mil)
<b>Width</b>	1/2 Inch