



3M Defense

- [Products](#)
- [Capabilities](#)
- [About 3M Defense](#)
- [Support](#)

[Contact Us](#)

[United States](#) > [All 3M Products](#) > [Market Segments](#) > [Manufacturing and Industry](#) > [3M Defense US](#) > [Defense Products](#) > [Tapes](#) > [Specialty Tapes](#) > [Scotch® Glass Cloth Electrical Tape 69-3/4"x66'](#), White, Silicone Adhesive, 3/4 in x 66 ft (19 mm x 20,1 m), 50 per case

Scotch® Glass Cloth Electrical Tape 69-3/4"x66', White, Silicone Adhesive, 3/4 in x 66 ft (19 mm x 20,1 m), 50 per case

3M ID 80018003600 UPC# 00054007099109 3M Product Number 69-3/4"X66'

[Print](#)



[Like](#) Be the first of your friends to like this.

This is a 7 mil woven glass cloth tape with a silicone pressure-sensitive adhesive. UL Recognized 180°C. Printable. Sold on a 1 inch core with an inner pack of 1 per box and 10 per carton.

Need Help?

Overview

Support

Scotch® Glass Cloth Tape 69 is edge-tear resistant conformable, high-temperature flame resistant adhesive; for use as a coil cover, anchor, for banding and core, layer and crossover insulation. Printable. Recommended for use with Scotch® Electric Arc-Proofing Tape 77.

Specifications

Adhesive Material	Silicone Thermoset Adhesive
Backing Material	Glass cloth
Breaking Strength	180 Pound Per Inch (Of Width)
China RoHS - Below MCV	Yes
Color	White
Dielectric Strength	3000 Volt
EU RoHS Compliant	Yes
Length	66 Linear Foot
Maximum Operating Temperature (Celsius)	200 Degree Celsius
Maximum Operating Temperature (Fahrenheit)	392 Degree Fahrenheit
Product Family	Scotch® Glass Cloth Electrical Tapes 69
Tape Color	White
Tape Grade	Premium

Tape Length	66 Linear Foot
Tape Type	Special Use
Tape Width	0.75 in
Thickness	7 Milli-inch (mil)
Width	0.75 Inch

3M Defense: [Products](#) | [Capabilities](#) | [About 3M Defense](#) | [Support](#) | [Contact Us](#)

3M: [News](#) | [Careers](#) | [Investor Relations](#) | [MSDS Search](#) | [Transport Information Search](#) | [A-Z Product Index](#) | [Contact 3M](#)

[Legal Information](#) | [Privacy Policy](#)

© 3M 2013. All Rights Reserved.

