
# 3M<sup>™</sup> Molded Assembly

2 mm x 2 mm 2M Series



- Available in multiple sizes
- Sockets mate with standard 2 mm × 2 mm headers and plugs
- Molded-in strain relief
- See Regulatory Information Appendix (RIA) for chemical compliance information

Date Modified: January 23, 2008

TS-2150-C Sheet 1 of 2

### **Physical**

#### **Connector:**

Technical Specification: TS-0525 for 2 mm  $\times$  2 mm Molded-On Socket

TS-2151 for  $2 \text{ mm} \times 2 \text{ mm}$  Molded-On PCB

Cable:

Technical Specification: TS-0452 for 1mm Flat Ribbon Cable

### **Electrical**


**Voltage Rating:** 30 V

### **Environmental**

**Temperature Rating:** -20°C to +105°C

## 3M<sup>™</sup> Molded Assembly

2 mm x 2 mm 2M Series



Length (Dim A) Tolerance								
Min.	Max.	Tol.						
1.7	10.0	±0.3						
10.0	20.0	±0.5						
20.0	40.0	±0.6						
40.0	120.0	±1.0						
120.0		±2.0						


Left Connector

Right Connector

Note: A fan-out assembly, with multiple connectors on one end, requires a drawing submittal and review.

Available Options															
Connector/Pos.	6	8	10	12	16	20	22	24	26	30	34	36	40	44	50
Socket	х	х	х		х	х	х	х	х	х	х		х	х	х
PCB	х	х	х	х	х	х			х	х		х	х	х	х
Cable	х	х	х	х	х	х	х	х	х	х	х	х	х	х	х
Cable/Pos.	6	8	10	12	16	20	22	24	26	30	34	36	40	44	50

Note: If "Keying" is required, mark the circuit(s) to key.



IR, IR

