



Solutions for Electronic Specialty Markets (ESM)

Product Catalog for Electronic Specialty Markets

- 3M™ Electronic Specialty Markets - New Product Releases
- 3M™ Abrasives
- 3M™ Adhesives, Cleaners & Compounds
- 3M™ Breadboards & Test Clips
- 3M™ Cable & Assemblies
- 3M™ Copper Interconnects
- 3M™ Fiber Optics
- 3M™ Fire Protection
- 3M™ Heat Shrink
- 3M™ Identification Systems
- 3M™ Occupational Health & Safety Products
- 3M™ Protective Bumpers
- 3M™ Reclosable Fasteners
- 3M™ Splicing, Terminating & Ducting
- 3M™ Static Control
- 3M™ Tapes
- 3M™ Terminals, Kits & Tools
- 3M™ Vacuums & Accessories
- 3M™ Warehousing & Packaging Supplies
- 3M™ Wire Connectors

Other Tools

- What's New
- Sales Contacts
- U.S. Distributors

[Product Catalog for Electronic Specialty Markets](#) >
 [3M™ Copper Interconnects](#) >
 [Headers](#) >

[Printer-friendly format](#) **2 mm x 2 mm, 1512 Series**

Straight or right angle, two row, high temperature header is IR, vapor, wave solder and industry standard compatible. Mates with boardmount and wiremount products. Has end- and side-stackable features. Maximizes use of PC board space.

Make a Selection

- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151208-7422-TB](#)
 8 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151210-7422-TB](#)
 10 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151212-7422-TB](#)
 12 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151220-7422-TB](#)
 20 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151224-7422-TB](#)
 24 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151230-7422-TB](#)
 30 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151240-7422-TB](#)
 40 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151244-7422-TB](#)
 44 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151250-7422-TB](#)
 50 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Right Angle, 1512 Series, 151260-7422-TB](#)
 60 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails
- 
[3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151208-8422-TB](#)
 8 Contacts, Pin Length .152", Plating 30µ" [0.76µm] Gold with Tin-Lead Solder Tails

 **Search This Product Catalog**

Search 2 mm x 2 mm, 1512 Series

Search all of Electronic Specialty Markets



- [3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151210-8422-TB](#)
10 Contacts, Pin Length .152", Plating 30μ" [0.76μm] Gold with Tin-Lead Solder Tails
- [3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151212-8422-TB](#)
12 Contacts, Pin Length .152", Plating 30μ" [0.76μm] Gold with Tin-Lead Solder Tails
- [3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151220-8422-TB](#)
20 Contacts, Pin Length .152", Plating 30μ" [0.76μm] Gold with Tin-Lead Solder Tails
- [3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151224-8422-TB](#)
24 Contacts, Pin Length .152", Plating 30μ" [0.76μm] Gold with Tin-Lead Solder Tails
- [3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151230-8422-TB](#)
30 contacts, straight angle, pin length .152", solder tail length .118", plating 30μ" [0.76μm] gold.
- [3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151240-8422-TB](#)
40 Contacts, Pin Length .152", Plating 30μ" [0.76μm] Gold with Tin-Lead Solder Tails
- [3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151250-8422-TB](#)
50 Contacts, Pin Length .152", Plating 30μ" [0.76μm] Gold with Tin-Lead Solder Tails
- [3M™ Pin Strip Header, 2 mm x 2 mm, Straight, 1512 Series, 151260-8422-TB](#)
60 Contacts, Pin Length .152", Plating 30μ" [0.76μm] Gold with Tin-Lead Solder Tails