### Previous Page | Print Page | Close Window





# GENERAL PURPOSE ROUND SPEAKERS

## Part Number: S200RA

MODEL NUMBER	S200RA
FRAME DIAMETER (MM)	50
FRAME DEPTH (MM)	18
MATERIAL: CONE / FRAME	PAPER / METAL
MAGNET TYPE	ALNICO
MAGNET: SIZE (MM) / WEIGHT (OZ/GRAMS)	13 x 10 - 0.35 / 9.92
RATED POWER (WATTS): Nom. / Max.	0.2 / 0.5
VOICE COIL IMPEDANCE (OHMS)	8 ± 15% @ 1000 Hz 1V
RESONANT FREQUENCY (Hz) Without Baffle	<u> </u>
FREQUENCY RESPONSE (Hz)	 Fo ~ 4500
OUTPUT SOUND PRESSURE LEVEL (S.P.L.)	83 + 3 dB
MEASURED AT:	 0.2W @ 50 CM 800
MEAN VALUE AT:	800, 1K, 1.2K, 1.5K Hz
OPERATION (MUST BE NORMAL)	PROGRAM SOURCE 0.2 W
BUZZ & RATTLES (MUST BE NORMAL)	SINE WAVE 0.2 W
DISTORTION @ RATED POWER INPUT	5% MAXIMUM @ 1,000 Hz
LOAD TEST (WHITE NOISE)	0.1 W @ 96 HOURS
HUMIDITY TEST*	40° ± 2°C 90% R.H. 96 HRS

HEAT TEST*	40° ± 2°C 50% R.H. 96 HRS
OUTSIDE DIAMETER OF YOKE SEAT (MM)	28.8 - YOKE SIZE: 22 x 14.2 x 12.5
OUTSIDE DIAMETER (ELIMINATE RIM)	44
BAFFLE OPENING (MM)	44
THICKNESS OF RIM (MM)	2.3
NET WEIGHT (OUNCES/GRAMS)	1.37 / 38.8

#### **POLARITY:**

DIAPHRAGM SHALL MOVE FORWARD WHEN APPLYING A POSITIVE DC CURRENT TO THE "+" (OR MARKED) TERMINAL.

\*SPEAKER MUST MEET NORMAL OPERATION AND BUZZ & RATTLES SPECIFICATIONS

#### DIMENSIONS

#### **TYPICAL FREQUENCY RESPONSE CURVE**

#### Return to top

All contents are Copyright © 1999 by International Components Corporation, All rights reserved. This site was developed and is maintained by Promptweb.com. For information, concerns or comments send e-mail to the webmaster. (webmaster@pw2.com)