

International Components Corporation

Tel: 631-952-9595 • 800-645-9154 • Fax: 631-952-9597 • Email: oemsales@icc107.com



SUB-MINIATURE LOW PROFILE ROUND SPEAKERS

Part Number: S150RLS

MODEL NUMBER	S150RLS
FRAME DIAMETER (MM)	38
FRAME DEPTH (MM)	8.0
MATERIAL - CONE / FRAME	PAPER / METAL
MAGNET TYPE	RARE EARTH
MAGNET: SIZE (MM) - WEIGHT (OUNCES/GRAMS)	12.5 x 1.5 - 0.056 / 1.4
RATED POWER (WATTS): Nom. / Max.	0.1 / 0.2
VOICE COIL IMPEDANCE (OHMS)	8 ± 15% @ 1000 Hz 1V
RESONANT FREQUENCY (Hz) Without Baffle	700 ± 20%
FREQUENCY RESPONSE (Hz)	Fo - 3,000 ± 10 dB
OUTPUT SOUND PRESSURE LEVEL (S.P.L.)	85 ± 3 dB
MEASURED AT:	0.2W @ 50CM
MEAN VALUE AT:	
OPERATION (MUST BE NORMAL)	800, 1.0, 1.2, 1.5K Hz
BUZZ & RATTLES (MUST BE NORMAL)	PROGRAM SOURCE 0.2W
DISTORTION @ RATED POWER INPUT	0.2W SINE WAVE
LOAD TEST (WHITE NOISE)	5% MAXIMUM @ 1,000 Hz
HUMIDITY TEST	0.2 W 5 HRS
	40°_+ 2°C 90% R.H. 48 HRS

HEAT TEST	40° + 2°C 50% R.H. 48 HRS
OUTSIDE DIAMETER OF YOKE SEAT (MM)	24 - YOKE SIZE: 17 x 14.2 x 3.5
OUTSIDE DIAMETER (ELIMINATE RIM)	35
BAFFLE OPENING (MM)	35
THICKNESS OF RIM (MM)	2.2
NET WEIGHT (OUNCES/GRAMS)	0.37 / 10.4

POLARITY:

DIAPHRAGM SHALL MOVE FORWARD WHEN APPLYING A POSITIVE DC CURRENT TO THE "+" (OR MARKED) TERMINAL.

*SPEAKER MUST MEET NORMAL OPERATION AND BUZZ & RATTLES SPECIFICATIONS

DIMENSIONS

■ TYPICAL FREQUENCY RESPONSE CURVE

Return to top

All contents are Copyright © 1999 by International Components Corporation, All rights reserved.

This site was developed and is maintained by Promptweb.com. For information, concerns or comments send e-mail to the webmaster. (webmaster@pw2.com)