

International Components Corporation

Tel: 631-952-9595 • 800-645-9154 • Fax: 631-952-9597 • Email: oemsales@icc107.com



MICRO MINIATURE LOW PROFILE ROUND SPEAKERS

Part Number: S150RMSS

MODEL NUMBER	S150RMSS
FRAME DIAMETER (MM)	36
FRAME DEPTH (MM)	3.8
MATERIAL - CONE / FRAME	MYLAR / ABS
MAGNET TYPE	RARE EARTH
MAGNET: SIZE (MM) - WEIGHT (OUNCES/GRAMS)	12.5 x 1.5 - 0.056 / 1.4
RATED POWER (WATTS): Nom. / Max.	0.1 / 0.2
VOICE COIL IMPEDANCE (OHMS)	8 ± 15%
RESONANT FREQUENCY (Hz) Without Baffle	420 + 20%
FREQUENCY RESPONSE (Hz)	Fo - 6,000 + 10 dB
OUTPUT SOUND PRESSURE LEVEL (S.P.L.)	82 + 3 dB
MEASURED AT:	1W @ 1M
MEAN VALUE AT:	800, 1.0, 1.2, 1.5K Hz
OPERATION (MUST BE NORMAL)	PROGRAM SOURCE 1 W
BUZZ & RATTLES (MUST BE NORMAL)	0.89 VOLTS - SINE WAVE
DISTORTION @ RATED POWER INPUT	
LOAD TEST (WHITE NOISE)	10% MAXIMUM @ 1000 Hz
HUMIDITY TEST	0.89 VOLTS - 5 HOURS
	N/A

HEAT TEST	N/A
OUTSIDE DIAMETER OF YOKE SEAT (MM)	VOICE COIL = 13.6
OUTSIDE DIAMETER (ELIMINATE RIM)	N/A
BAFFLE OPENING (MM)	33
THICKNESS OF RIM (MM)	2.8
NET WEIGHT (OUNCES/GRAMS)	0.17 / 4.8

POLARITY:

DIAPHRAGM SHALL MOVE FORWARD WHEN APPLYING A POSITIVE DC CURRENT TO THE "+" (OR MARKED) TERMINAL.

*SPEAKER MUST MEET NORMAL OPERATION AND BUZZ & RATTLES SPECIFICATIONS

DIMENSIONS

■ TYPICAL FREQUENCY RESPONSE CURVE

Return to top

All contents are Copyright © 1999 by International Components Corporation, All rights reserved.

This site was developed and is maintained by Promptweb.com. For information, concerns or comments send e-mail to the webmaster. (webmaster@pw2.com)