

International Components Corporation

Tel: 631-952-9595 • 800-645-9154 • Fax: 631-952-9597 • Email: oemsales@icc107.com




PC MOUNT SPEAKERS

Part Number: S110R-PCRev.1


MODEL NUMBER	S110R-PC
FRAME DIAMETER (MM)	30
FRAME DEPTH (MM)	12
MAGNET TYPE	RARE EARTH
RATED POWER (WATTS): Nom. / Max.	0.15 / 0.2
VOICE COIL IMPEDANCE (OHMS)	8 ± 15%
RESONANT FREQUENCY (Hz)	1000 +/- 20%
FREQUENCY RESPONSE (Hz)	550 ~ 5,500
SOUND OUTPUT LEVEL (dB)	> 82 ± 3 dB @ 1.5 KHz, 10 CM
OPERATING TEMPERATURE (°C)	-40°C ~ +70°C
MATERIAL - CONE / FRAME	MYLAR / NORYL
NET WEIGHT (GRAMS)	10.0
MOUNTING DIMENSIONS (MM)	2 PIN - 15mm

THESE SPEAKERS ARE AVAILABLE, ON A SPECIAL ORDER BASIS, IN A VARIETY OF VOICE COIL IMPEDANCES. THE MOST COMMON IMPEDANCES ARE 4, 16, 32, 45, AND 100 OHMS

■ DIMENSIONS



■ FREQUENCY



Return to top

All contents are Copyright © 1999 by International Components Corporation, All rights reserved.

This site was developed and is maintained by Promptweb.com. For information, concerns or comments send e-mail to the webmaster. (webmaster@pw2.com)